



Surface mount transient voltage suppressor power 400 watts

Stand-Off Voltage: 5.0V~440V

FEATURES


- For surface mounted applications in order to optimize board space.
- Low profile package
- Glass passivated junction
- Low inductance
- Plastic package has Underwriters Laboratory Flammability

MECHANICAL DATA

- Case: SMA
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.055g / 0.002oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Maximum Ratings and Electrical characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation on $T_A=25^{\circ}\text{C}$ (Note 1,2,4, Fig1)	P_{PPM}	400	W
Peak Forward Surge Current (Note 3, Fig 4)	I_{FSM} (UNI)	60	A
Peak Pulse Current on 10/1000 us waveform (Note 1, Fig 3)	I_{PPM}	see Table 1	A
ESD Voltage per IEC61000-4-2 Contact Air	V_{ESD1} V_{ESD2}	± 30 ± 30	kV
Typical Thermal Resistance Junction to Ambient(Note 2)	$R_{\theta JA}$ $R_{\theta JC}$ $R_{\theta JL}$	100 20 25	$^{\circ}\text{C/W}$
Operating Junction Temperature and Storage Temperature Range	T_j, T_{stg}	-55 ~ +150	$^{\circ}\text{C}$

NOTES:

1. Non-repetitive current pulse, per Fig.3 and derated above $T_A = 25^{\circ}\text{C}$ per Fig. 2.
2. Mounted on 5mm² copper pads to each terminal.
3. Peak Forward Surge Current : 8.3ms single half sine-wave Superimposed on rated load (JEDEC method).
4. Peak pulse power waveform is 10/1000μS.



Characteristics at Ta=25°C

Table 1

Type		Marking		V _{RMW}	Breakdown Voltage		Test Current	Max. Reverse Leakage	Max.Clamp Voltage	Max. Peak Pulse Current
					V _{BR} @ I _T		I _T	IR@VR	V _c @ I _{pp}	I _{pp}
					Min	Max				
UNI	BI	UNI	BI	V	V	V	mA	μA	V	A
SMAJ5.0A	SMAJ5.0CA	AE	WE	5	6.4	7	10	800	9.2	43.5
SMAJ6.0A	SMAJ6.0CA	AG	WG	6	6.67	7.37	10	800	10.3	38.8
SMAJ6.5A	SMAJ6.5CA	AK	WK	6.5	7.22	7.98	10	500	11.2	35.7
SMAJ7.0A	SMAJ7.0CA	AM	WM	7	7.78	8.6	10	200	12	33.3
SMAJ7.5A	SMAJ7.5CA	AP	WP	7.5	8.33	9.21	1	100	12.9	31
SMAJ8.0A	SMAJ8.0CA	AR	WR	8	8.89	9.83	1	50	13.6	29.4
SMAJ8.5A	SMAJ8.5CA	AT	WT	8.5	9.44	10.4	1	20	14.4	27.8
SMAJ9.0A	SMAJ9.0CA	AV	WV	9	10	11.1	1	10	15.4	26
SMAJ10A	SMAJ10CA	AX	WX	10	11.1	12.3	1	5	17	23.5
SMAJ11A	SMAJ11CA	AZ	WZ	11	12.2	13.5	1	1	18.2	22
SMAJ12A	SMAJ12CA	BE	XE	12	13.3	14.7	1	1	19.9	20.1
SMAJ13A	SMAJ13CA	BG	XG	13	14.4	15.9	1	1	21.5	18.6
SMAJ14A	SMAJ14CA	BK	XK	14	15.6	17.2	1	1	23.2	17.2
SMAJ15A	SMAJ15CA	BM	XM	15	16.7	18.5	1	1	24.4	16.4
SMAJ16A	SMAJ16CA	BP	XP	16	17.8	19.7	1	1	26	15.4
SMAJ17A	SMAJ17CA	BR	XR	17	18.9	20.9	1	1	27.6	14.5
SMAJ18A	SMAJ18CA	BT	XT	18	20	22.1	1	1	29.2	13.7
SMAJ20A	SMAJ20CA	BV	XV	20	22.2	24.5	1	1	32.4	12.3
SMAJ22A	SMAJ22CA	BX	XX	22	24.4	26.9	1	1	35.5	11.3
SMAJ24A	SMAJ24CA	BZ	XZ	24	26.7	29.5	1	1	38.9	10.3
SMAJ26A	SMAJ26CA	CE	YE	26	28.9	31.9	1	1	42.1	9.5
SMAJ28A	SMAJ28CA	CG	YG	28	31.1	34.4	1	1	45.4	8.8
SMAJ30A	SMAJ30CA	CK	YK	30	33.3	36.8	1	1	48.4	8.3
SMAJ33A	SMAJ33CA	CM	YM	33	36.7	40.6	1	1	53.3	7.5
SMAJ36A	SMAJ36CA	CP	YP	36	40	44.2	1	1	58.1	6.9
SMAJ40A	SMAJ40CA	CR	YR	40	44.4	49.1	1	1	64.5	6.2
SMAJ43A	SMAJ43CA	CT	YT	43	47.8	52.8	1	1	69.4	5.8
SMAJ45A	SMAJ45CA	CV	YV	45	50	55.3	1	1	72.7	5.5
SMAJ48A	SMAJ48CA	CX	YX	48	53.3	58.9	1	1	77.4	5.2
SMAJ51A	SMAJ51CA	CZ	YZ	51	56.7	62.7	1	1	82.4	4.9
SMAJ54A	SMAJ54CA	RE	ZE	54	60	66.3	1	1	87.1	4.6
SMAJ58A	SMAJ58CA	RG	ZG	58	64.4	71.2	1	1	93.6	4.3
SMAJ60A	SMAJ60CA	RK	ZK	60	66.7	73.7	1	1	96.8	4.1
SMAJ64A	SMAJ64CA	RM	ZM	64	71.1	78.6	1	1	103	3.9
SMAJ70A	SMAJ70CA	RP	ZP	70	77.8	86	1	1	113	3.5
SMAJ75A	SMAJ75CA	RR	ZR	75	83.3	92.1	1	1	121	3.3
SMAJ78A	SMAJ78CA	RT	ZT	78	86.7	95.8	1	1	126	3.2
SMAJ85A	SMAJ85CA	RV	ZV	85	94.4	104	1	1	137	2.9
SMAJ90A	SMAJ90CA	RX	ZX	90	100	111	1	1	146	2.7
SMAJ100A	SMAJ100CA	RZ	ZZ	100	111	123	1	1	162	2.5
SMAJ110A	SMAJ110CA	SE	VE	110	122	135	1	1	177	2.3
SMAJ120A	SMAJ120CA	SG	VG	120	133	147	1	1	193	2.1
SMAJ130A	SMAJ130CA	SK	VK	130	144	159	1	1	209	1.9
SMAJ150A	SMAJ150CA	SM	VM	150	167	185	1	1	243	1.6
SMAJ160A	SMAJ160CA	SP	VP	160	178	197	1	1	259	1.5
SMAJ170A	SMAJ170CA	SR	VR	170	189	209	1	1	275	1.5
SMAJ180A	SMAJ180CA	ST	VT	180	201	222	1	1	292	1.4
SMAJ200A	SMAJ200CA	SV	VV	200	224	247	1	1	324	1.2
SMAJ220A	SMAJ220CA	SX	VX	220	246	272	1	1	356	1.1
SMAJ250A	SMAJ250CA	SZ	VZ	250	279	309	1	1	405	1
SMAJ300A	SMAJ300CA	TE	UE	300	335	371	1	1	486	0.8
SMAJ350A	SMAJ350CA	TG	UG	350	391	432	1	1	567	0.7
SMAJ400A	SMAJ400CA	TK	UK	400	447	494	1	1	648	0.6
SMAJ440A	SMAJ440CA	TM	UM	440	492	543	1	1	713	0.6



Fig.1 Peak Pulse Power Rating Curve




Fig.2 Forward Current Derating Curve




Fig.3 Pulse Waveform





Fig.4 Maximum Non-Repetitive Peak Forward Surge Current






PACKAGE OUTLINE


Plastic surface mounted package; 2 leads

SMA



UNIT		A	D	E	H _E	c	e	g	b	a
mm	max	2.2	4.5	2.7	5.2	0.31	1.6	1.5	0.2	0.3
	min	1.9	4.0	2.3	4.7	0.15	1.3	0.9	0.05	
mil	max	87	181	106	205	12	63	59	7.9	12
	min	75	157	91	185	6	51	35	2	

The recommended mounting pad size





Important Notice and Disclaimer

Jingdao Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Jingdao Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Jingdao Microelectronics assume any liability for application assistance or customer product design.

Jingdao Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Jingdao Microelectronics.

Jingdao Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of Jingdao Microelectronics.