








Part No	Pin	A	B	Part No	Pin	A	B
BX-0.8-2PWT	2	0.80	3.85	BX-0.8-14PWT	14	10.40	13.45
BX-0.8-3PWT	3	1.60	4.65	BX-0.8-15PWT	15	11.20	14.25
BX-0.8-4PWT	4	2.40	5.45	BX-0.8-16PWT	16	12.00	15.05
BX-0.8-5PWT	5	3.20	6.25	BX-0.8-17PWT	17	12.80	15.85
BX-0.8-6PWT	6	4.00	7.05	BX-0.8-18PWT	18	13.60	16.65
BX-0.8-7PWT	7	4.80	7.85	BX-0.8-19PWT	19	14.40	17.45
BX-0.8-8PWT	8	5.60	8.65	BX-0.8-20PWT	20	15.20	18.25
BX-0.8-9PWT	9	6.40	9.45	BX-0.8-21PWT	21	16.00	19.05
BX-0.8-10PWT	10	7.20	10.25	BX-0.8-22PWT	22	16.80	19.85
BX-0.8-11PWT	11	8.00	11.05	BX-0.8-23PWT	23	17.60	20.65
BX-0.8-12PWT	12	8.80	11.85	BX-0.8-24PWT	24	18.40	21.45
BX-0.8-13PWT	13	9.60	12.65				

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 0.8
- 2.Voltage Rating: 30V AC DC
- 3.Current Rating: 0.5A AC DC
- 4.Insulation Resistance: 100MQ Min
- 5.Contact Resistance: 20mQ Max
- 6.Withstanding voltage: 200V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

2	端子 Contact	黄铜	n×1	电镀铜: 整个表面镀层30u"MIN,厚镀层 80u"MIN.
1	基座 Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES				DRAWN BY				
0.X	±0.25	X.°	±3°	CHK.BY				
0.XX	±0.12			APRV.BY				
0.XXX ±0.05 X.X° ±0.5°					SHEET	PROD. NAME		WAFER 0.8 卧贴
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1	PART NO.		BX-0.8-nPWT
MM	A4	1:1			TITLE			