






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



SCHEMATIC



PCB LAYOUT

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Terminals	SMT pins
Storage Temperature	- 30° C to85° C

Packaging:
Bulk packaging.
Tape & reel for the SMT type:
Reels of 1,000 pieces for 4.3 and 5.0 mm height
Reels of 700 pieces for 7.0 mm height
Reels of 700 pieces for 7.3 mm height
Reels of 500 pieces for 9.5 mm height
Reels of 400 pieces for 13.0 mm height

Mechanical

Actuation Force	Operating Force(gf)	H	Height mm
		43	4.3
L	130±50	50	5.0
M	160±50	70	7.0
H	200±50	73	7.3
K	260±50	95	9.5
R	320±50	13	13.0

X. ±0.50	X.° ±2°
.X ±0.30	.X° ±1°
.XX ±0.10	.XX° ±0.5°
.XXX ±0.05	

UNITS
mm

MAT'L

FINISH

Q'TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS 645 S X X GS


TITLE:
TACTILE SWITCH (G SMT)

APPD: ROGER

DWG NO. :
YTS 645 S X X GS

CHKD: ROC

DR: BILLY WANG 2020/08/21



SCALE	SHEET	REV.
1/1	1/1	A1