







Part No	Pin	A	B	Part No	Pin	A	B
BX-0.8-2PLT	2	0.80	3.85	BX-0.8-14PLT	14	10.40	13.45
BX-0.8-3PLT	3	1.60	4.65	BX-0.8-15PLT	15	11.20	14.25
BX-0.8-4PLT	4	2.40	5.45	BX-0.8-16PLT	16	12.00	15.05
BX-0.8-5PLT	5	3.20	6.25	BX-0.8-17PLT	17	12.80	15.85
BX-0.8-6PLT	6	4.00	7.05	BX-0.8-18PLT	18	13.60	16.65
BX-0.8-7PLT	7	4.80	7.85	BX-0.8-19PLT	19	14.40	17.45
BX-0.8-8PLT	8	5.60	8.65	BX-0.8-20PLT	20	15.20	18.25
BX-0.8-9PLT	9	6.40	9.45	BX-0.8-21PLT	21	16.00	19.05
BX-0.8-10PLT	10	7.20	10.25	BX-0.8-22PLT	22	16.80	19.85
BX-0.8-11PLT	11	8.00	11.05	BX-0.8-23PLT	23	17.60	20.65
BX-0.8-12PLT	12	8.80	11.85	BX-0.8-24PLT	24	18.40	21.45
BX-0.8-13PLT	13	9.60	12.65				

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 0.8
- 2.Voltage Rating: 30V AC DC
- 3.Current Rating: 0.5A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 200V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

2	端子 Contact	黄铜	n×1	电镀铜: 整个表面镀层30u"MIN, 厚镀铜 80u"MIN.
1	基座 Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES				DRAWN BY			
0.X	±0.25	X.°	±3°	CHK.BY			
0.XX	±0.12			APRV.BY			
0.XXX	±0.05	X.X°	±0.5°		SHEET	PROD. NAME	WAFER 0.8 立贴
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1	PART NO.	BX-0.8-nPLT
MM	A4	1:1				TITLE	