

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PBT
Max.Processing Temp: 200°C for30-60seconds
(220°C for5seconds)

P/N	PIN	DIM.A	DIM.B
2.54DC2-01-03PZS	2*3	5.08	26.92
2.54DC2-01-04PZS	2*4	7.62	29.46
2.54DC2-01-05PZS	2*5	10.16	32.00
2.54DC2-01-06PZS	2*6	12.70	34.54
2.54DC2-01-07PZS	2*7	15.24	37.08
2.54DC2-01-08PZS	2*8	17.78	39.60
2.54DC2-01-10PZS	2*10	22.86	44.70
2.54DC2-01-12PZS	2*12	27.94	49.78
2.54DC2-01-13PZS	2*13	30.48	52.30
2.54DC2-01-15PZS	2*15	35.56	57.40
2.54DC2-01-17PZS	2*17	40.64	62.50
2.54DC2-01-20PZS	2*20	48.26	70.10
2.54DC2-01-25PZS	2*25	60.96	82.85
2.54DC2-01-30PZS	2*30	73.66	95.40
2.54DC2-01-32PZS	2*32	78.74	100.48

PART NUMBER DESCRIPTION:


2.54DC2-01-NPZS

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;06.....64PIN)

(排针开关)



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54DC2-NPIn H17 180度 PC3.8 PBT	
			PAR	2.54DC2-01-NPZS
DECIMALS:	ANGLES:		DWN	
X.±0.30	X°±5'		CHKD	
X.X±0.25	X.X°±1'		APVD	
X.XX±0.20	X.XX°±0.5'		SCALE N:A	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1	 REV:A