

5552209-1

✓ ACTIVE


## CHAMP

TE Internal #: 5552209-1

Plug, Cable-to-Board, 14 Position, 2.16 mm [.085 in] Centerline, 2 Row, Standard Profile, Vertical, Mating Retention, PCB D-Sub Connectors

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Plug Assembly: Vertical, 2.16mm



Connector & Housing Type: Plug

Connector System: **Cable-to-Board**

Number of Positions: **14**

Centerline (Pitch): **2.16 mm [.085 in]**

Number of Rows: **2**

[All D-Sub Plug Assembly: Vertical, 2.16mm \(4\)](#)

## Features

### Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	14
Number of Rows	2
PCB Mount Orientation	Vertical

### Body Features

Primary Product Color	Black
Connector Profile	Standard

### Contact Features

Contact Options	Installed
	30 $\mu$ in
Contact Mating Area Plating Material	Gold, Gold Flash
Contact Underplating Material	Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze

### Termination Features

Rectangular Termination Post & Tail Thickness	.25 mm [.01 in]
Rectangular Termination Post & Tail Width	.5 mm [.019 in]
Termination Method to PCB	Through Hole - Solder

### Mechanical Attachment

Mounting Feature Material	Thermoplastic
PCB Mount Retention	Without
Mating Retention	With
Mating Retention Type	Screwlocks
Connector Mounting Type	Board Mount

### Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.16 mm [.085 in]

### Dimensions

PCB Thickness (Recommended)	1.57 mm, 2.36 mm, 3.18 mm [.062 in] [.093 in] [.125 in]
Row-to-Row Spacing	4.3 mm [.169 in]

### Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Shielded	No
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	85
Packaging Method	Tray

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 5552243-1  
ASSY, PLUG, 64 POS, VERT MTG

## Customers Also Bought




TE Part #1-2349815-2  
D3950 REC 8POSN. 1ROW X KEY  
MARKED



TE Part #900412-2  
PC I/O RETENTION LEG ASSY 80P



TE Part #1473226-1  
SOCKET WITH RING MINI U-M-N-L



TE Part #2-1586038-2  
22P VRT HDR VAL-U-LOK V0



TE Part #2013874-1  
ME CONN (M) DUMMY PLUG ASSY



TE Part #2229093-1  
MOD JACK ASSEMBLY V-TYPE H=21.7mm



TE Part #2309223-1  
RITS CONN.HDR ASSY 4ROW 4P THR W TAPE



TE Part #ASA021N00210235000  
623 PLUG



TE Part #1-5316316-0  
.6FHP08H,140,S,GIG,08/Sn,HT,SEYes

## Documents

### Product Drawings

ASSY, PLUG, 14 POS, VERT MTG

English