


CRYSTAL UNITS

Automotive Grade

ACTUAL SIZE: ☐

CXAF-032000

CERAMIC PACKAGE



APPLICATIONS

- ▶ Camera
- ▶ TPMS
- ▶ Bluetooth

FEATURES

- ▶ Seam Seal
- ▶ Excellent Solderability
- ▶ Excellent Vibration Resistance & Shock Resistance
- ▶ High Frequency Stability
- ▶ Excellent Thermal Hysteresis
- ▶ RoHS Compliant
- ▶ IATF-16949 Certified
- ▶ AEC-Q200 Qualified

Specification

MODEL

DIMENSION	(mm)	2.00 X 1.60
-----------	--------	-------------

FREQUENCY

FREQUENCY RANGE (Fundamental)	MHz	16.000 ~ 96.000
FREQUENCY RANGE (3rd Overtone)	MHz	100.000 ~ 125.000
FREQUENCY TOLERANCE (25°C)	ppm	± 10 ~ ± 100
FREQUENCY STABILITY (Ref to 25°C)	ppm	± 20 ~ ± 100 ± 50 ~ ± 100

ENVIRONMENTAL CONDITION

OPERATING TEMPERATURE RANGE	°C	- 40 ~ + 85 Or - 40 ~ + 125	- 55 ~ + 125
STORAGE TEMPERATURE RANGE	°C	- 55 ~ + 150	
AGING / YEAR	ppm	± 3	

ELECTRICAL SPECIFICATIONS

TEST CIRCUIT		S&A 250B With π Fixture
LOAD CAPACITANCE	pF	SERIES, 6pF to 47pF, or Specify
DRIVE LEVEL	uW	15, 30, 50, 100, 200 or special requirement
EQUIVALENT SERIES RESISTANCE	Ω	See Table
SHUNT CAPACITANCE	pF	2.0 Max.

*Specification subject to change without notice.

Equivalent Series Resistance (Ω)

Frequency Range	Mode of Operation	ESR
16.000 ~ 19.199	Fundamental	150 Ω Max.
19.200 ~ 21.999	Fundamental	100 Ω Max.
22.000 ~ 35.999	Fundamental	80 Ω Max.
36.000 ~ 96.000	Fundamental	60 Ω Max.
100.000 ~ 125.000	3rd Overtone	120 Ω Max.

Dimension(mm)

CXAF-032000

