




1

2

3

4

5

6

7

8

RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

H

H

G

G

F

F

E

E

D

D

C

C


B

B

A

A

SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



- 1)MATERIAL:
HOUSING:LCP S475 UL 94V-0
CONTACT:C5191
SHELL:SUS304-H
- 2)FINISH:
CONTACT:GOLD FLASH PLATED ON CONTACT AREA;
GOLD FLASH PLATED ON SOLDER TAILS,
- 3)ELECTRICAL CHARACTERISTICS
RATING CURRENT : 0.5A MAX.
CONTACT RESISTANCE :50 mΩ MAX
DIELECTRIC WITHSTANDING : 500V AC MIN.
INSULATION RESISTANCE: 1000 MΩ MIN.
- 4)MECHANICAL CHARACTERISTICS
MATING CYCLE :3000 CYCLES

RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED MATAL MASK T=0.12mm

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. SIM20210-6P211-H135	TITLE: 1.35H 6PIN PUSH PUSH MICRO SIM CARD CONNECTOR		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N: A	1/1