



Features

- Low gate charge
- Low C_{RSS} (typ 13pF)
- Fast switching
- 100% avalanche tested
- Improved dv/dt capability
- RoHS product



Applications

- High frequency switching mode power supply
- Electronic ballast based on half bridge
- LED power supplies



Absolute Ratings (Tc=25°C)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	1000	V
Drain Current-continuous	I_D T=25°C T=100°C	12	A
		8	A
Drain Current-pulse (note 1)	I_{DM}	20*	A
Gate-Source Voltage	V_{GS}	±30	V
Single pulse avalanche energy (note 2)	E_{AS}	1166	mJ
Avalanche Current (note 1)	I_{AR}	3	A
Repetitive Avalanche Energy(note 1)	E_{AR}	90	mJ
Power Dissipation (MS12N100FC/FT)	PD TC=25°C Derate above 25°C	367	W
		2.9	W/°C
Power Dissipation (MS12N100FE)	PD TC=25°C Derate above 25°C	100	W
		0.8	W/°C
Power Dissipation (MS12N100FS)	PD TC=25°C Derate above 25°C	68	W
		0.54	W/°C

Operating and Storage Temperature Range	T_J, T_{STG}	-55~+150	°C
Maximum Lead Temperature for Soldering Purposes	T_L	300	°C

*Drain current limited by maximum junction temperature

Electrical Characteristics($T_{CASE}=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Tests conditions	Min	Type	Max	Units
Drain-Source Voltage	BV_{DSS}	$I_D=250\mu\text{A}, V_{GS}=0\text{V}$	1000	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=V_{DSS}, V_{GS}=0\text{V}, T_C=25^{\circ}\text{C}$	-	-	1	μA
		$V_{DS}=V_{DSS}, T_C=125^{\circ}\text{C}$	-	-	10	μA
Gate body leakage current	I_{GSS}	$V_{DS}=0\text{V}, V_{GS}=\pm 30\text{V}$	-	-	± 100	nA
On-Characteristics						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	2.0	-	4.0	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10\text{V}, I_D=1\text{A}, T_C=25^{\circ}\text{C}$	-	1.0	1.2	Ω
Forward Transconductance	g_{FS}	$V_{DS}=40\text{V}, I_D=6\text{A}$ (note 4)	-	16	-	S
Dynamic Characteristics						
Input capacitance	C_{iss}	$V_{DS}=25\text{V}, V_{GS}=0\text{V}, f=1.0\text{MHz}$	-	1584	-	pF
Output capacitance	C_{oss}		-	166	-	pF
Reverse transfer capacitance	C_{rss}		-	12	-	pF

Electrical Characteristics($T_{CASE}=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Tests conditions	Min	Type	Max	Units
Switching-Characteristics						
Turn-On delay time	$t_{d(on)}$	$V_{DD}=600\text{V}, I_D=12\text{A}, R_{GEN}=25\Omega$ (note 4,5)	-	24	-	ns
Turn-On rise time	t_r		-	46	-	ns
Turn-Off delay time	$t_{d(off)}$		-	118	-	ns
Turn-Off rise time	t_f		-	58	-	ns
Total Gate Charge	Q_g	$V_{DS}=800\text{V}, I_D=12\text{A},$	-	41	-	nC

Gate-Source charge	Q _{gs}	V _{GS} =10V (note 4,5)	-	9	-	nC
Gate-Drain charge	Q _{gd}		-	16	-	nC
Drain-Source Diode Characteristics and Maximum Ratings						
Diode Forward Voltage (note 3)	V _{SD}	V _{GS} =0V,I _S =1A	-	-	1.2	V
Maximum Pulsed Drain-Source Diode Forward Current	I _{SM}	-	-	-	110	A
Maximum Continuous Drain Source Diode Forward Current	I _S	-	-	-	12	A
Reverse recovery time	t _{rr}	V _{GS} =0V, I _S =8A dI _F /dt=100A/μs (note 4)	-	620	-	ns
Reverse recovery charge	Q _{rr}		-	4.39	-	μC

Thermal Characteristic

Parameter	Symbol	Value			Unit
		MS12N10 0FC/FT	MS12N10 0FE	MS12N100 FS	
Thermal Resistance, junction to Case	$R_{th(j-C)}$	0.4	1.25	1.84	$^{\circ}C/W$
Thermal Resistance, Junction to Ambient	$R_{th(j-A)}$	36	62.5	62.5	$^{\circ}C/W$

Order information


Order codes	Package	Packaging
MS12N100FC	TO-247	Tube
MS12N100FE	TO-263	Tube
MS12N100FT	TO-220	Tube
MS12N100FS	TO-220F	Tube

Notes:


1. Pulse width limited by maximum junction temperature
2. $L=15mH, I_{AS}=12A, V_{DD}=50V, R_G=25 \Omega$, Starting $T_J=25^{\circ}C$
3. $I_{SD} \leq 12A, di/dt \leq 300A/\mu s, V_{DD} \leq BV_{DSS}$, Starting $T_J=25^{\circ}C$
4. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$
5. Essentially independent of operating temperature

ELECTRICAL CHARACTERISTICS (curves)


On-Region Characteristics@25°C




Extended On-Region Characteristics@25°C




On-Region Characteristics@125°C




Transfer Characteristics









Transconductance




On-Resistance Variation vs Drain Current and Gate Voltage





Transient Thermal Response Curve



PACKAGE MECHANICAL DATA

