




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		H	REVISED PER ECO-11-006183	27SEP11	KH	JO



MATERIAL:

RECEPTACLE CONTACTS-	PHOSPHOR BRONZE
RECEPTACLE HOUSING:	LCP; BLACK
TERMINATING COVERS:	POLYESTER; BLACK



PLATING:
 RECEPTACLE CONTACTS- 0.00076 [.000030] MINIMUM GOLD PLATE IN CONTACT AREA,
 0.00127 [.000050] MINIMUM BRIGHT TIN-LEAD PLATE IN TERMINATION AREA,
 ALL OVER 0.00127 [.000050] MINIMUM NICKEL

3. RECOMMENDED WIRE:
28 AWG- 0.91 [.036] MAX O.D. PVC OR POLYETHYLENE INSULATION.

4. SHORT-LONG CONTACT SEQUENCE MUST ALTERNATE BUT MAY BEGIN WITH EITHER A SHORT OR LONG CONTACT.



OBSOLETE PART NUMBER.



PLATING:
RECEPTACLE CONTACTS- 0.00076 [0.00030] MINIMUM GOLD PLATE IN CONTACT AREA,
0.00127 [0.00050] MINIMUM TIN PLATE IN TERMINATION AREA,
ALL OVER 0.00127 [0.00050] MINIMUM NICKEL.


7. TERMINATION COVERS MUST BE ORDERED SEPARATELY.




ROHS 2002/95/EC COMPLIANT.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	6-104893-0	
	65.48 [2.578]	57.56 [2.266]	55.58 [2.200]	44	90	5-104893-9	
	59.13 [2.328]	51.21 [2.016]	49.53 [1.950]	39	80	5-104893-8	
	52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	5-104893-7	
	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	5-104893-6	
	40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	5-104893-5	
	33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	5-104893-4	
	27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	5-104893-3	
	21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	5-104893-2	
	14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	5-104893-1	
		76.96 [3.030]	43.59 [1.716]	41.91 [1.650]	33	68	1-104893-1
		71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	1-104893-0
65.48 [2.578]		57.56 [2.266]	55.58 [2.200]	44	90	104893-9	
59.13 [2.328]		51.21 [2.016]	49.53 [1.950]	39	80	104893-8	
	52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	104893-7	
	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	104893-6	
	40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	104893-5	
	33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	104893-4	
	27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	104893-3	
	21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	104893-2	
	14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	104893-1	
	FINISH	D	C	B	A	NO. OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17-6-93 J. HERRINGTON		 TE Connectivity	
DIMENSIONS: mm [INCHES]		C/P S. FREMICHAH 24-6-93 APP'D D. DUPLER			
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		D. PLC ± —		108-1443	
		1. PLC ± —		APPLICATION SPEC	
		3. PLC ± —		114-7010	
		4. PLC ± —		WEIGHT —	
		ANGLES ± —		CUSTOMER DRAWING	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO	
		SEE TABLE		A1 00779 C 104893	
				RESTRICTED TO	
				SCALE 10:1 SHEET 1 OF 1 REV H	