


SPECIFICATION

- 1.Rating : DC 20V 20A;
- 2.Contact resistance: ≤0.03Ω;
- 3.Insulation resistance: ≥100MΩ (DC250V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 5-40N;
- 6.life test: 5,000 cycles。

1	SHELL	1	C3604	Ni60u"
2	SPRING PIECE	1	C18400 T=0.40	Au0.7-1.5u" Over Ni50u"
3	HOUSING	1	PBT +30%GF UL 94V-0	BLACK
No.	DESCRIPTION	QTY	MATERIAL	PLATING

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	DC PIUG
CHKD		UNIT: mm/in	PART NO.: DT-5525020
APPD		SIZE: A4	DWG NO.:

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	