

Image-Reject Mixer

15 - 45 GHz



MAMX-011043-DIE

Rev. V1

Features

- Low Conversion Loss: 9 dB
- High Linearity: 18 dBm IIP3
- High Image Rejection: 20 dBc
- Wide IF Bandwidth: DC to 10 GHz
- High Isolation
- Die Size: 1.40 × 1.90 × 0.10 mm
- RoHS* Compliant

Applications

- Test & Measurement, Microwave Radio, and Radar

Description

MAMX-011043-DIE is an image-reject passive diode mixer MMIC. The mixer offers low conversion loss, high linearity, high image rejection and a wide IF bandwidth. The image-reject circuit configuration provides excellent port isolation while internal 50 Ω matching simplifies its application.

This mixer is well suited for applications such as test and measurement, microwave radio and radar.


MAMX-011043-DIE is also available in a 4 mm QFN package. Refer to datasheet MAMX-011043.

Ordering Information

Part Number	Package
MAMX-011043-DIE	Vacuum Release Gel Pack ¹
MAMX-011043-SB2	Sample Board

1. Die quantity varies.

Functional Schematic



Bond-pad Configuration

Pin #	Function
2	LO
1, 3, 4, 7, 8, 10	Ground ²
5	IF1
6	IF2
9	RF
11	Ground ³

2. These pads are internally connected to ground, and they can be left unconnected.

3. The backside of the die must be connected to RF, DC and thermal ground.

* Restrictions on Hazardous Substances, compliant to current RoHS EU directive.

Electrical Specifications^{4,5}: $F_{IF} = 100 \text{ MHz}$, $P_{LO} = +16 \text{ dBm}$, $T_A = 25^\circ\text{C}$, $Z_0 = 50 \Omega$

Parameter	Test Conditions	Units	Min.	Typ.	Max.
LO and RF Frequency	—	GHz	15	—	45
IF Frequency	—	GHz	0	—	10
LO Power	—	dBm	—	16	—
Conversion Loss	15 - 45 GHz	dB	—	9	10.5
Input P1dB	—	dBm	—	8	—
Input IP3	$P_{RF} = -10 \text{ dBm/tone}$, $\Delta f = 1 \text{ MHz}$	dBm	—	18	—
Input IP2 (Half IF)	$P_{RF} = -10 \text{ dBm/tone}$, $\Delta f = 1 \text{ MHz}$	dBm	—	40	—
LO-to-RF Isolation	—	dB	—	40	—
LO-to-IF Isolation	—	dB	—	40	—
RF-to-IF Isolation	—	dB	—	30	—
Image Rejection	15 - 42 GHz 42 - 45 GHz	dBc	15 14	20	—
Amplitude Imbalance	—	dBc	—	± 1	—
Phase Imbalance	—	°	—	± 10	—
RF Return Loss	RF = 36 GHz	dB	—	7	—
IF Return Loss	IF = 2 GHz	dB	—	10	—

4. All specifications refer to down-conversion operation, unless otherwise noted.

5. Characterization measurements were taken using RF probes, with I/O port configuration shown in Assembly Guideline Diagram on page 7.

Absolute Maximum Ratings^{6,7}

Parameter	Absolute Maximum
LO Power	23 dBm
RF or IF Power	20 dBm
Junction Temperature ⁸	+150°C
Operating Temperature	-55°C to +85°C
Storage Temperature	-65°C to +150°C

6. Exceeding any one or combination of these limits may cause permanent damage to this device.

7. MACOM does not recommend sustained operation near these survivability limits.

8. Operating at nominal conditions with $T_J \leq +150^\circ\text{C}$ will ensure MTTF > 1×10^6 hours.

Handling Procedures

Please observe the following precautions to avoid damage:

Static Sensitivity

These electronic devices are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these HBM Class 1B devices.

Image-Reject Mixer

15 - 45 GHz




MAMX-011043-DIE


Rev. V1

Typical Performance Curves: 90° Hybrid @ 100 MHz IF


**Down Conversion Gain (Upper Side Band)
over LO Drive**




**Down Conversion Image Rejection (Upper Side Band)
over LO Drive**




**Down Conversion Gain (Upper Side Band)
over Temperature**



**Down Conversion Image Rejection (Upper Side Band)
over Temperature**



**Down Conversion Gain (Lower Side Band)
over LO Drive**



**Down Conversion Image Rejection (Lower Side Band)
over LO Drive**




Image-Reject Mixer

15 - 45 GHz




MAMX-011043-DIE


Rev. V1

Typical Performance Curves: 90° Hybrid @ 100 MHz IF


Up Conversion Gain (USB) over LO Drive




Up Conversion SSB (USB) over LO Drive




Down Conversion IIP2 (USB) over LO Drive




Down Conversion IIP3 (USB) over LO Drive



Down Conversion P1dB (USB) Over LO Drive




Down Conversion Isolation




Typical Performance Curves:


Amplitude Imbalance




Phase Imbalance



RF Return Loss



IF Return Loss



IF Bandwidth




Image-Reject Mixer 15 - 45 GHz



MAMX-011043-DIE

Rev. V1

MxN Spurious Rejection @ IF Port

RF = 15.1 GHz @ -10 dBm

LO = 15 GHz @ +16 dBm

All values in dBc below, the IF output power level

MxRF	NxLO				
	0	1	2	3	4
0	X	14	53	56	X
1	17	0	36	57	57
2	81	62	49	59	97
3	87	97	57	53	61
4	X	X	X	95	80


LO Harmonics

LO = +16 dBm

All values in dBc below,
input LO level measured at RF

n LO spur at RF port				
LO GHz	1	2	3	4
14	62	59	51	N/A
16	54	61	58	N/A
18	49	50	N/A	N/A
20	48	48	N/A	N/A
22	49	44	N/A	N/A
24	48	45	N/A	N/A
26	47	N/A	N/A	N/A
30	44	N/A	N/A	N/A
45	40	N/A	N/A	N/A


Hybrid Configuration



External Hybrid

- Down conversion and Up conversion data captured with external hybrid 90° coupler part number: Innovative IPP-2345.
- RF Upper Side Band (USB) mode connect hybrid 0° port to IF1 mixer port, 90° hybrid port to IF2 mixer port.
- RF Lower Side Band (LSB) mode connect hybrid 0° port to IF2 mixer port, 90° hybrid port to IF1 mixer port.


Assembly Guideline



Attach bare die to PCB or carrier using conductive epoxy. Bond die signal pads to PCB 50 Ω traces using 1 mil gold wire. Double bond wire is recommended on RF and LO pads for optimal performance. There is no need to bond the die ground pads.

Caution: Exposed airbridges are incorporated in the circuit layout on the top surface of this die. These airbridges are sensitive in structure and due care should be taken when handling the die.

Outline Drawing



Bondpad Table ^{9,10}

Pad #	Pad Name	Size-X	Size-Y
1	GND1	90 μm	90 μm
2	LO	150 μm	90 μm
3	GND2	90 μm	90 μm
4	GND3	90 μm	90 μm
5	IF1	90 μm	90 μm
6	IF2	90 μm	90 μm
7	GND4	90 μm	90 μm
8	GND5	90 μm	90 μm
9	RF	150 μm	90 μm
10	GND6	90 μm	90 μm

9. Units are in microns with a tolerance of $\pm 5 \mu\text{m}$, except for die exterior dimensions which are street-center-to-street-center – nominal kerf, $\pm 20 \mu\text{m}$ tolerance.

10. Die thickness is $100 \pm 10 \mu\text{m}$.

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.