




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # EGA201N00000800000 915 ITEC RECEPTACLE, ANGLED	 TE Part # EGA201N00000851000 915 itec receptacle angl rotatable 25x25	 TE Part # EGC101N00000006000 615/915 YTEC RECEPTACLE, ANGLED	 TE Part # EGC201N00000805000 915 ITEC RECEPTACLE, ANGLED
 TE Part # EEA201N00000500000 915 ITEC RECEPTACLE	 TE Part # EEA201N00000501000 915 ITEC RECEPTACLE	 TE Part # EEA201N00000506000 915 ITEC RECEPTACLE	 TE Part # EEA201N00000508000 915 ITEC RECEPTACLE

Customers Also Bought

 TE Part #926300-1 6P UNIV.M-N-L.PLUG	 TE Part #1-141708-2 MOD-4 REC.CONT.SCP.	 TE Part #42770-2 250 FASTON FLAG TAB 18-14 AWG TPBR	 TE Part #EKA201N00330500000 915 EXTENSION
 TE Part #EKB001N00310001000 615 EXTENSION	 TE Part #ESA002N00320001000 615 EXTENSION	 TE Part #HSA202N00420100000 723 HTEC PLUG, SPEEDTEC	 TE Part #926302-1 10& UNIV.M-N-L.PLUG
 TE Part #EKB201N00310500000 915 EXTENSION	 TE Part #2260269-1 F07A APF PLUG CABLE ASSY L150		



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ESA202N00320500000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ESA202N00320500000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ESA202N00320500000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ESA202N00320500000

English

fuer Datenblaetter, die online konfigurierbar sind

German