

3-5175475-9  ACTIVE

CHAMP | CHAMP .050 Series I

TE Internal #: 3-5175475-9

PCB Mount Receptacle, Vertical, Board-to-Board, 80 Position, 1.27 mm [.05 in] Centerline, Gold, Through Hole - Solder, Signal, CHAMP .050 Series I

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **80**

Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	80

Electrical Characteristics

Insulation Resistance	1 MΩ
Operating Voltage	250 VAC

Body Features

PCB Retention Feature Material	Brass
PCB Retention Feature Plating Material	Tin over Nickel
Connector Profile	Standard

Contact Features

PCB Contact Termination Area Plating Material Thickness	1 µm[39.4 µin]
Contact Layout	Inline

Mating Tab Width	.8 mm[.031 in]
Mating Tab Thickness	.32 mm[.013 in]
Contact Shape & Form	Single Tine, Square
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.5 μ m[19.7 μ in]
Contact Type	Socket
Contact Current Rating (Max)	1 A

Termination Features

Rectangular Termination Post & Tail Thickness	.32 mm[.013 in]
Rectangular Termination Post & Tail Width	.5 mm[.02 in]
Termination Post & Tail Length	3.1 mm[.122 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Boardlock, Retention Leg
Mating Alignment	With
Mating Alignment Type	Polarized
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	Nylon - GF

Dimensions

Connector Height	7 mm[.275 in]
	.5 in

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity

70

Packaging Method

Tray

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024
(241)
Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 3-5175473-9
CHAMP 050 B/B PLUG V W/LG 80P

Also in the Series | CHAMP .050 Series I





IDC D-Sub Connectors(6)



PCB Headers & Receptacles(134)

Customers Also Bought

TE Part #1623786-1
SQM2 10R 5% (WIRE)TE Part #1437565-5
FSM103-12MM,TACTILE,PB SWITCHTE Part #2108614-5
2.7H SPRING FINGER WITH EMBOSSEDTE Part #1-284539-2
12 POS TERMI-BLOK 900 W.S.F 3,TE Part #2344655-7
PCB ANT, MHF 4, 150mm, Wi-Fi
TRIPLE BANDTE Part #5179031-4
0.8FH,P08H.5,100,08/Sn,TUTE Part #292161-3
CT P/HDR ASSY V 3P W/KINK NATTE Part #1513317-1
PCB ANTENNA PENTA BANDTE Part #8-2176422-2
TLRP 2512 3.0W R005 1% 75PPM 4K RL

Documents

Product Drawings

[CHAMP 050 B/B REC V W/LEG 80P](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_3-5175475-9_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_3-5175475-9_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_3-5175475-9_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English