


PC card drilling dimensions(after plating)  
(thickness 1.60±0.20mm)






GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

#### LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	5.90	D09P33E4U*00LF	D09P33E6U*00LF
15	39.14	33.32	25.18	25.12	19.18	5.90	D15P33E4U*00LF	D15P33E6U*00LF
25	53.03	47.04	39.12	38.84	33.12	5.70	D25P33E4U*00LF	D25P33E6U*00LF
37	69.32	63.50	55.68	55.30	49.68	5.70	D37P33E4U*00LF	D37P33E6U*00LF

200 Mating 500 Mating

X--> ØT = UNC 4-40  
L--> ØT = M3

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB					
ltr ecn no dr date				tolerances unless otherwise specified		 MM		scale 2:1		title					
D ELX-I-21045 AB 2015/06/04				angles linear						MALE DELTA-D RIGHT ANGLE					
										WITH NUT & METAL PLATE					
				0°±2'											
				dr JOHN SLEEBA		2003/12/27				dwg no		sheet 1 of 1		size	
				enrg ALIAS BABU		2015/06/04				C01—8646—0851		A3			
				chr MITHUN PAUL		2015/06/04									
				appd BIJU K PAUL		2015/06/04									
sheet index		revision sheet		D 1											