





RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table				
PART NO	Pin	A	B	C
W1501130-2PW2431	2	1.50	6.00	3.65
W1501130-3PW2431	3	3.00	7.50	5.15
W1501130-4PW2431	4	4.50	9.00	6.65
W1501130-5PW2431	5	6.00	10.50	8.15
W1501130-6PW2431	6	7.50	12.00	9.65
W1501130-7PW2431	7	9.00	13.50	11.15
.....				
W1501130-16PW2431	16	22.50	27.00	24.65

NOTES:
1.BASE: LCP
2.PIN: Brass
3.Solder Tab: Brass
SPECIFICATIONS:
1.Spacing: 1.5
2.Voltage Rating: 250V AC DC
3.Current Rating: 1A AC DC
4.Insulation Resistance: 500MΩ Min
5.Contact Resistance: 20mΩ Max
6.Withstanding voltage: 500V AC 1/Minute
7.Temperatuer Range: -25℃ ~+ 85℃

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.* ±5°	PART NO.	TITLE:
.XX ±0.20	X.X* ±1°	W1501130-XPW2431	WAFER 1.50 立贴
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1