




料带图 比例 :1:2

技术要求 Specification:

- 1、 材质 : 磷青铜, 表面镀锡
Material: Phos. Bronze Tin-Plated
- 2、 适用线规 Applicable wire: AWG#30-#24;
- 3、 零件外观不得有有害毛刺、尖角、锐边和机械损伤;
表面镀层应均匀、光亮、无雾斑、剥层等缺陷;
Parts may not have the appearance of harmful burrs, sharp corners, sharp edges and mechanical damage, surface coatings should be uniform, bright, no fog spots, delamination and other defects.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. W2002-DZ211	TITLE: PH2.0MM TERMINAL		
.XX ±0.20	X.X* ±1°				
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE N:A	SHEET 1/1
		APPD: Sophia			