




NOTES:


- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

PIN number variable size comparison table

Part No	PIN	A	B	C
W1252120-2PW2431	2	1.25	7.50	
W1252120-3PW2431	3	2.50	8.75	
W1252120-4PW2431	4	3.75	10.00	2.50
W1252120-5PW2431	5	5.00	11.25	3.75
W1252120-6PW2431	6	6.25	12.50	5.00
W1252120-7PW2431	7	7.50	13.75	6.25
W1252120-8PW2431	8	8.75	15.00	7.50
W1252120-9PW2431	9	10.00	16.25	8.75
W1252120-10PW2431	10	11.25	17.50	10.00
W1252120-11PW2431	11	12.50	18.75	11.25
W1252120-12PW2431	12	13.75	20.00	12.50
W1252120-13PW2431	13	15.00	21.25	13.75
W1252120-14PW2431	14	16.25	22.50	15.00
W1252120-15PW2431	15	17.50	23.75	16.25
W1252120-16PW2431	16	18.75	25.00	17.50

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.* ±5°	PART NO. W1252120-XPW2431	TITLE: WAFER 1.25 卧贴
.XX ±0.20	X.X* ±1°		
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	
			SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1