


3M™ Textool™ 0.65 mm pitch, Open Top, BGA Test & Burn-In Sockets

Type II



34

- Accommodates a wide range of package thicknesses without requiring socket adaptations.
- Allows excellent air flow around device.
- Includes a retractable locating guide for easy board mounting, even with hundreds of leads.
- Compatible with most robotic handlers.
- Easy manual operation.
- Double beam contact delivers balanced, opposing forces to solder ball with minimal shear stress.
- Contact tips touch ball above its center plane, producing only slight indentations and negligible ball deformation.
- Package Retainer Option
- At user's request, sockets can be equipped with mechanical package retainers. This option provides additional holdown protection for high shock or vibration environments.

Date Issued: December 13, 2002

TS-9600-02
Sheet 1 of 2

Physical

Body:

Material: Polyethersulfone (PES)
Flammability: UL 94V-0
Color: Black

Contact:

Material: Beryllium Copper
Plating: Gold over Nickel

Other Metal Parts: Stainless Steel

Marking: 3M Logo/Textool

Electrical

Insulation Resistance: >1000MΩ at 100 Vdc

Dielectric Withstanding Voltage: 100 Vrms at Sea Level

Initial Contact Resistance: <50mΩ measured at 1.0 mA applied current

Current Rating: 0.5 A max @ 25°C

Environmental

Operating Temperature Rating: - 55 °C to + 150 °C

Mechanical

Durability: 20,000 actuations (10,000 devices load/unload) at room temperature

Initial Contact Force: 8.5gf (0.087N) Nom for 0.4 mm diameter solder ball

Initial Operating Force: Type II – 5Kg Max @ Full Pin Count

Contact Wiper Gap - Fully Open: 0.55 mm Nom


3M Electronic & Interconnect Solutions Division

6801 River Place Blvd.
Austin, TX 78726-9000

For technical, sales or ordering information call 800-225-5373
or visit our website: www.3M.com/eisd

3M™ Textool™ 0.65 mm pitch, Open Top, BGA Test & Burn-In Sockets

Type II



Ordering Information

PACKAGE SPECIFICATIONS	
Max Package Size	17.0 ± 0.10 mm SQ Max
Max Matrix	25 x 25 Max
Ball Diameter	0.35 - 0.45 mm Min
Ball Height	0.30 mm Min

P.C.B. RECOMMENDATIONS	
Board Thickness	1.6 mm
Through Hole Diameter	0.22 mm Min