





RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	TITLE: 4.2MM WAFER DIP TYPE	
X.X ±0.30	X.° ±5°		PART NO. W420120K-XPB2123	
.XX ±0.20	X.X° ±1°	DESIGN: James	CUSTOMER	SIZE A4
.XXX ±0.10	X.XX° ±0.5°	CHED: Talen		UNITS MM
MANUFACTURE DWG		APPD: Sophia		SCALE N:A
				SHEET 2/2



VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
W420120K-2PW2123	2*1	0.00	5.40
W420120K-4PW2123	2*2	4.20	9.60
W420120K-6PW2123	2*3	8.40	13.80
W420120K-8PW2123	2*4	12.60	18.00
W420120K-10PW2123	2*5	16.80	22.20
.....			
W420120K-24PW2123	2*12	46.20	51.60

2	端子 Contact	黄铜	N*1	表面镀锡
1	基座 Wafer	PA66UL94V-2	1	白色
序号	名称	材料	数量	备注

- 技术指标:
1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
 2. 额定电压: 250V AC, DC.
 3. 耐电压: 1500V AC/minute.
 4. 接触电阻: $\leq 20\text{m}\Omega$.
 5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
 6. 额定电流: 5A AC, DC.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. W420120K-XPW2123		TITLE: 4.2MM WAFER DIP TYPE	
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia			SCALE
				N:A	1/2