





技术要求 :

1. 塑件材料 :PA66 (UL-94V-0)
2. 接触件 :黄铜镀锡
3. 接触电阻 :≤20mΩ
4. 绝缘电阻 :≥1000MΩ
5. 额定电压 :250V AC DC
6. 额定电流 :3.0A AC DC
7. 耐压 :能承受 1000V AC/Minute
8. 工作温度 : -25° ~ +85°
9. 可焊性试验 :浸锡面积 ≥ 95% 温度 235 ⁺⁵₋₀°, 时间 2.5±0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

PIN number variable size comparison table			
PART NO	PIN	A	B
W396111K-2PY2113	2	3.96	7.92
W396111K-3PY2113	3	7.92	11.88
W396111K-4PY2113	4	11.88	15.84
W396111K-5PY2113	5	15.84	19.80
W396111K-6PY2113	6	19.80	23.76
.....			
W396111K-20PY2113	20	(20-1)x3.96	(20+1)x3.96

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u"MIN, 再镀 锡 80u"MIN
1	基座 Wafer	LCP (UL94V-0)	1	米色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	W396111K-XPY2113	VH3.96MM 直针 带扣
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE
		APPD: Sophia	UNITS
			A4
			MM
			SCALE
			SHEET
			N:A
			1/1