



UHF Hybrid Junction 5 MHz-1GHz

H-1-4

- Broad Frequency Range
- 0°-180° Hybrid with High Isolation

Guaranteed Specifications *

(From - 55°C to + 85°C)


Frequency Range	5 MHz-1 GHz	
Isolation (A-B Ports)	5-300 MHz	50 dB Min
	300 MHz-1 GHz	40 dB Min

Operating Characteristics

Impedance	50 Ohms Nominal	
A & B Ports	100 Ohms Nominal	
C & D Ports	7 Watts Max	
Input Power	Linear with Frequency	
Phase Shift (A to C or D)	(-45° @ 300 MHz)	
Environmental	See Appendix for MIL-STD-883 screening option.	

* All specifications apply with 50 ohm source and load impedance.
This product contains elements protected by United States Patent 3,311,650.


Functional Diagram



Ordering Information

Model No.	Package
H-1-4 BNC	Connectorized
H-1-4 N	Connectorized
H-1-4 SMA	Connectorized



C-33



Dimensions in () are in mm.

See Appendix for complete physical dimensions.

Typical Performance



Specifications Subject to Change Without Notice.

MA-COM Inc. 1011 Pawtucket Boulevard, Lowell, MA 01853 USA

Telephone: 800-366-2266

2-248

0°
3C
LC
Gu
(For
Fret
Inter
(Less

H
21

Ampl
VSW

Isola

Plas

Op
Impe
Input

Env
See
This p
Fu

Or
Moc
H-9
H-9

Spec
M/A