




SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

PIN number variable size comparison table			
PART NO	PIN	DIM. A	DIM. B
B20010130-2PB0513-H20C28	2*1	0.00	2.00
B20010130-4PB0513-H20C28	2*2	2.00	4.00
B20010130-6PB0513-H20C28	2*3	4.00	6.00
B20010130-8PB0513-H20C28	2*4	6.00	8.00
B20010130-10PB0513-H20C28	2*5	8.00	10.00
B20010130-12PB0513-H20C28	2*6	10.00	12.00
B20010130-14PB0513-H20C28	2*7	12.00	14.00
B20010130-16PB0513-H20C28	2*8	14.00	16.00
B20010130-18PB0513-H20C28	2*9	16.00	18.00
.....			
B20010130-80PB0513-H20C28	2*40	(40-1)x2.0	(40)x2.0

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. B20010130-APB0513-H20C28	TITLE: 2.0PH H2.0 2xnPin 180度 PC2.8 PA3.9 PB2.0 L8.7 6T		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1