




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insrlator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)

PIN number variable size comparison table

PART NO	PIN	DIM. A	DIM. B
B25430130-6PB0513-H89C32	2*3	5.08	7.62
B25430130-8PB0513-H89C32	2*4	7.62	10.16
B25430130-10PB0513-H89C32	2*5	10.16	12.70
B25430130-12PB0513-H89C32	2*6	12.70	15.24
B25430130-14PB0513-H89C32	2*7	15.24	17.78
B25430130-16PB0513-H89C32	2*8	17.78	20.32
B25430130-18PB0513-H89C32	2*9	20.32	22.86
B25430130-20PB0513-H89C32	2*10	22.86	25.40
B25430130-24PB0513-H89C32	2*12	27.94	30.48
B25430130-26PB0513-H89C32	2*13	30.48	33.02
B25430130-28PB0513-H89C32	2*14	33.02	35.56
B25430130-30PB0513-H89C32	2*15	35.56	38.10
B25430130-32PB0513-H89C32	2*16	38.10	40.64
B25430130-34PB0513-H89C32	2*17	40.64	43.18
.....			
B25430130-64PB0513-H89C32	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO.		TITLE:	
.XX ±0.20	X.X° ±1°	B25430130-APB0513-H89C32		2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T	
.XXX ±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)