

# NetKey® NK6™ Category 6 U/UTP Copper Cable – Europe

Category 6 cable shall meet the ISO 11801 Class E and ANSI/TIA-568-C.2 Category 6 channel standards. The conductors shall be 24 AWG insulated with polyethylene. The copper conductors shall be twisted in pairs, separated by a cross divider and covered by a LSFRZH jacket.



## technical information

<b>Electrical performance:</b>	Certified channel performance in a 4-connector configuration up to 100 meters and meets ISO 11801 Class E and ANSI/TIA-568-C.2 Category 6 standards at swept frequencies up to 250MHz.
<b>Conductors/insulators:</b>	24 AWG solid copper insulated with polyolefin
<b>Flame rating:</b>	EN 50575: Euroclass B2ca-s1a-d1-a1
<b>PoE compliance:</b>	Meets IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt for PoE applications
<b>Installation tension:</b>	110 N (25 lbf)
<b>Temperature rating:</b>	-20° C to 75° C (-4° F to 167° F) during operation 0° C to 50° C (32° F to 122° F) during installation
<b>Cable jacket:</b>	LSFRZH
<b>Cable diameter:</b>	5.9mm (0.235 inch) nominal
<b>Cable weight:</b>	12kg/305m (26 lbs./1000 ft.)
<b>Packaging:</b>	305m (1000 ft.) easy payout carton

## key features and benefits

<b>Easy payout carton</b>	Ensures proper performance and provides quick installation
<b>Third party tested</b>	Cable has been tested as part of the NetKey™ Category 6 U/UTP Copper Cabling System by an independent laboratory and complies with the electrical channel requirements of the following standards: ISO 11801 Class E and ANSI/TIA-568-C.2 Category 6
<b>Descending length cable marking</b>	Easy identification of remaining cable reduces installation time and cable scrap
<b>Robust design</b>	Cross divider separates twisted pairs for robust cable design

## applications

NK6™ U/UTP Copper Cable is a component of the Panduit NK6™ U/UTP Copper Cabling System. This end-to-end system provides Gigabit Ethernet performance with usable bandwidth beyond 250MHz. With certified performance the ISO 11801 Class E and ANSI/TIA-568-C.2 Category 6 standards, this system will support the following applications:

- \* Ethernet 10BASE-T
- \* 100BASE-T (Fast Ethernet)
- \* 1000BASE-T (Gigabit Ethernet)

# PANDUIT®

## DATA SHEET

### NetKey® Network Components

#### NetKey® UTP Copper Cable

**LSFRZH:** NUW6C04\*\*-CE

#### NetKey® Category 6 UTP Jack Module

**Punchdown:** NK688MIW\*

#### NetKey® Category 6 UTP Patch Cords – CM

**Foot lengths:** NK6PC3^Y  
**Meter lengths:** NK6PC1M^^Y

#### NetKey® Category 6 Punchdown Patch Panels

**12-port:** NK6PPG12WY  
**24-port, 1 RU:** NK6PPG24Y  
**48-port, 2 RU:** NK6PPG48Y

#### NetKey® Category 6 All Molded Punchdown Patch Panels

**24-port, 1 RU:** NK6PP24P  
**48-port, 2 RU:** NK6PP48P

#### NetKey® Flush Mount Modular Patch Panels

**Angled, 24-port, 1 RU:** NKPPA24FMY  
**Angled, 48-port, 2 RU:** NKPPA48FMY  
**Flat, 24-port, 1 RU:** NKPP24FMY  
**Flat, 48-port, 2 RU:** NKPP48FMY

#### NetKey® Category 6 All Molded Modular Patch Panels

**24-port, 1 RU:** NKPP24P  
**48-port, 2 RU:** NKPP48P

### Termination and Cable Prep Tools

#### JackRapid™

**Termination Tool:** JR-PAN-2

**Conductor stripping tool:** CWST

**Conductor stripping tool:** CFAST

\*\* Part number available in WH (White). For additional colors, please contact Panduit Customer Service.

\*For standard colors other than Off White (IW), replace suffix with EI (Electrical Ivory), IG (International Gray), WH (White), BL (Black), BU (Blue), RD (Red), YL (Yellow), GR (Green), or VL (Violet). Add -Q to end of part number for 25 pack convenience package.

^For standard foot lengths other than 3 feet, replace the 3 in the part number with 5, 7, 10, 14 or 20. For standard colors other than Off White, add suffix BU (Blue), RD (Red), YL (Yellow) or GR (Green) before the Y at the end of the part number. For example, the part number for a blue, Category 6, 5-foot patch cord is NK6PC5BUY.

^^For standard meter lengths other than 1 meter, replace the 1 in the part number with 2, 3, 4 or 5. For standard colors other than Off White, add suffix BU (Blue), RD (Red), YL (Yellow) or GR (Green) before Y at the end of the part number. For example, the part number for a blue, Category 6, 5-meter patch cord is NK6PC5MBUY.


Fluke JackRapid™ Termination Tool available through distribution. To locate the local office, visit [www.flukenetworks.com/contact](http://www.flukenetworks.com/contact). JackRapid™ is a trademark of Fluke Networks.

# NetKey® NK6™ Category 6 U/UTP Copper Cable – Europe

## additional specifications

Mechanical Test	
Ultimate Breaking Strength	>400 N (90 lbf.)
Minimum Bend Radius	4 x cable diameter
Electrical Test	
Nominal Velocity of Propagation (NVP)	65%

## cable construction



### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT®**

©2018 Panduit Corp.  
ALL RIGHTS RESERVED.  
NKDS61--WW-ENG  
4/2018