





RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE


PIN number variable size comparison table			
PART NO	PIN	DIM. A	DIM. B
B20020120-1PB0513-H43C28	1	0.00	2.00
B20020120-2PB0513-H43C28	2	2.00	4.00
B20020120-3PB0513-H43C28	3	4.00	6.00
B20020120-4PB0513-H43C28	4	6.00	8.00
B20020120-5PB0513-H43C28	5	8.00	10.00
.....			
B20020120-40PB0513-H43C28	40	(40-1)x2.0	(40)x2.0

SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 2.0FH H4.3 1xnPin 180度 W2.4 U型 PC2.8 6T		
.XX ±0.20	X.X* ±1°	B20020120-APB0513-H43C28	CUSTOMER	SIZE	UNITS
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James		A4	MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1