





芯数	3	4	5	6	8
额定电流/电压	3A/60V	3A/60V	3A/30V	1.5A/30V	1.5A/30V
额定脉冲电压	800V	800V	800V	800V	800V
绝缘阻抗 (MΩ)	≥500	≥500	≥500	≥500	≥500
接触阻抗 (MΩ)	≤5	≤5	≤5	≤5	≤5



Pin Assignments(Front View)



5	M8 焊线式公针	黄铜	镀金	pc	3~8
4	M8 锁板六角螺母 M8×1	黄铜	镀镍	pc	1
3	M8 壳体防水0型圈Ø9×Ø6×1.5	橡胶	/	pc	1
2	M8 双切边板前公座外壳	黄铜	镀镍	pc	1
1	M8 短体公胶芯	尼龙	/	pc	1
No.	Specification	Material	Treat	Unit	Q'ty

		The View		dosinconn DOSIN INDUSTRIAL(HK)CO.,LTD CONNECTION & CABLE ASSEMBLY		Web:http://www.dosinconn.com Dosin2005@dosin-china.com Tel:(0086)769-81153906 Fax:(0086)769-81875836	
单位 unit	mm	页码 page	1/1	江门市德索连接器有限公司 Jiangmen Dosin Connector Co., LTD		产品名称 M8 公头后锁 焊杯外露 Product name	
图号 Drawing NO		料号 Part Number		DS869MCS0284		绘图 Draw drawing	FuLiu
文件保密 File security This drawing shall not be copied, circulated or used for other purposes without permission. 本图纸未经许可, 不可复制、外传或它用		未注公差 Unmarked tolerance		审核 Check		客户确认 Customer confirmation	
		零部件 Parts X. ±0.5 X.X ±0.20 X.XX ±0.10		线性 Line ≤10 ±1 10~50 ±1.5 >50 ±4%			
		角度 angle ±3°					