





SPECIFICATIONS
Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:−40°to+105°
Insrlator Material:Polyester(UL94V−0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:
240°C for30−60seconds
(260°C for5seconds)

PIN number variable size comparison table			
PART NO	PIN	DIM. A	DIM. B
B10020820-1PB0513-H20C28	1	0.00	1.00
B10020820-2PB0513-H20C28	2	1.00	2.00
B10020820-3PB0513-H20C28	3	2.00	3.00
B10020820-4PB0513-H20C28	4	3.00	4.00
B10020820-5PB0513-H20C28	5	4.00	5.00
B10020820-6PB0513-H20C28	6	5.00	6.00
B10020820-7PB0513-H20C28	7	6.00	7.00
B10020820-8PB0513-H20C28	8	7.00	8.00
B10020820-9PB0513-H20C28	9	8.00	9.00
.....			
B10020820-40PB0513-H20C28	40	(40-1)	40

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. B10020820-APB0513-H20C28	TITLE: 1.0FH H2.0 1xnPin SMT W1.5 U型 PC2.8 PB2.3 6T (左前右后)		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1