



SPECIFICATIONS

Rated Current:2.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:800MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Resistance To Soldering Heat:
260°C±5°C, 10s(PA6T&PA9T&LCP insulator)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

3320 XX M XX X X L X 0X

No. of Pins
6—64



Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Insulator Material
Option
C=BK-PA6T
E=BK-PA9T
F=BK-LCP

Color Type
B=Black
G=Grey

Latch Type
L=Long Latch

Packing
0=PE Bag
A=Tray
T=Tube



				OPERATION		DRAW	YiYuSheng	19.10.05	SCALE	FIT	JILN ® 深圳锦凌电子股份有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30							
				X.XX	±0.20	CHECK			UNIT	mm	PART NO.	
				X.XXX	±0.10				SIZE	A4		
				Angle	±3°	APPROVE			SHEET	1/1	TITLE:	
				DIM	TOL				PROJ.			
A0	2019.10.05	NEW DRAWING									3320XXMXXXXLX0X	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE							2.0 ejector header Npin SMT 长耳	