





RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	DIM. A	DIM. B
B25410130-2PB0513-H25A60	2*1	0.00	2.54
B25410130-4PB0513-H25A60	2*2	2.54	5.08
B25410130-6PB0513-H25A60	2*3	5.08	7.62
B25410130-8PB0513-H25A60	2*4	7.62	10.16
B25410130-10PB0513-H25A60	2*5	10.16	12.70
.....			
B25410130-80PB0513-H25A60	2*40	(40-1)X2.54	(40)X2.54

SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20MΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Copper Alloy
Standard: PBT
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 200°C for 30-60seconds
(220°C for 5seconds)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. B25410130-APB0513-H25A60	TITLE: 2.54PH H2.5 2xNPin 180#PC3.0 PA6.0 PB2.5 L11.5 PBT		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen			SCALE N:A
		APPD: Sophia			
				SCALE N:A	SHEET 1/1