





SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S





Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE±0.05)



Ordering Information

14	10	12	XX	X	X	XX	M	XXX	X	XX
No. of Pins Per Row 02~50P	Insulator Material Option C=BK-PA6T F=BK-LCP	Post W=With Post N=W/O Post	Contact G1:1u" Gold G2:1.5u" Gold G3:2u" Gold G4:3u" Gold G5:5u" Gold G6:10u" Gold G7:15u" Gold G8:30u" Gold S0:Gold Flash/Tin SN:Tin	Plating	Pin Length	Packing A=Tray T=Tube P=Tube+Cap R=Reel+Cap	code stream 01~99			



Dimension antitheses list			
ITEM	PA	PB	W
Alternate	4.00	1.50	5.30

				OPERATION		DRAW	YiYuSheng	12.04.18	SCALE	FIT	JiLN® 深圳锦凌电子股份有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	SIZE	A4					
				X.XXX	±0.10	CHECK			SHEET	1/1	PART NO.	141012XXXXXXMXXXXXX
A0	2012.04.18	NEW DRAWING		Angle	±3°				SHEET	1/1	TITLE:	1.27PH 2xNpin H1.0 SMT
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE			PROJ.			