








XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: LCP,UL94V-0,BLACK

TERMINAL 端子: PHOSPHOR BRONZE ,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.10 mm/S

INSERTION FORCE 插入力: 2.0KG.F MAX

Withdrawal Force 拔出力: 44N Max.

OPERATING TEMPERATURE 工作温度: 0°C~+85°C.

STORAGE TEMPERATURE 储存温度: -40°C~+80°C.




ELECTRICAL 电动:

RATED VOLTAGE 额定电压:150 VOLTS AC

CURRENT RATING 额定电流:1.5A AC

DIELECTRIC STRENGTH 介电强度:500V AC ,2mA shall be applied between
adjacent contacts for 1 minute at 50 or 60 Hz.INSULATION RESISTANCE 绝缘电阻:500 MEGA OHMS MIN.INITIAL
AFTER 500V DC FOR 1 MINUTE

CONTACT RESISTANCE 接触电阻:100mΩ or less

DIMENSIONS OF PC BOARD HOLES
TOLERANCE:±0.05(PRINTED-SIDED VIEW)

广东星坤科技股份有限公司

X 生 日期
X 教
MARK 文件工程章

REVISIONS

DATE

REVISED

APPROVED

UNSPECIFIED TOLERANCES

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 3.1 TYPE C
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	DWG NO.:
APPD		SIZE: A4	X05ADGWW6SBL1
		WEIGHT	SHEET
			1/1
		REVISION	A0