







NOTES:

备注

1.Copper,nickel base,matte tin

黄铜H62, 镍底, 镀雾锡

2.Wire screw hole M4

压线螺孔M4

3.Current Rating: 50A

额定电流: 50A

4.Operating temperature: -40℃ ~ +125℃

工作温度: -40℃ ~ +125℃

5.There shall be no defects such as pin deformation and burrs.

不得有脚变形, 毛刺等缺陷

6.Unmarked dimensions refer to tolerances

未标注的尺寸参考公差



Ordering Information

XD - * * * * - * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	Dip	Product No.	Material
M=Full Teeth (插针)	3=M3 (螺牙)	(焊脚)	(防止扭动)	0808=8x8mm	S=Snit F=Flag Dip	产品序号	默认=Copper (黄铜) R=Red Copper (紫铜)
RN=Silver Nut (银螺母)	4=M4 (螺牙)	2=2个		1014=10x14mm			
RG=Silver Gasket (银垫片)	5=M5 (螺牙)	4=4个					
	6=M6 (螺牙)	6=6个					
	8=M8 (螺牙)	8=8个					



GENERAL TOLERANCE

制图

02

DIM TOL

审核

X.X ±0.30

批准

X.XX ±0.20

比例

X.XXX ±0.10

SCALE

Angle ±3.0°

投影



深圳讯答科技有限公司

ShenzhenXunDaTechnology Co.,Ltd

产品名称

PCB 焊接端子 (插板 铜垫片 M4 4焊脚 8x8x9.6mm)

版本

A

产品料号

XD-RG44-0808-D053-02

单位

mm

材料

页次

1/1

1 初版发行

变更内容

MODIFY CONTENT

日期

MODIFY DATE