

CMH107N20

200V, 8.2mΩ typ., 110A N-Channel MOSFET

General Description

The CMH107N20 uses advanced SGT technology to provide excellent RDS(ON). This device is ideal for high-frequency switching and synchronous rectification.

Features

- Low On-Resistance
- 100% avalanche tested
- Low Gate Charge
- RoHS Compliant


Product Summary

BVDSS	RDS(on) max.	ID
200V	10mΩ	110A

Applications

- Motor control and drive
- Battery management
- Uninterruptible Power Supply

TO-247 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	200	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current	110	A
I _D @T _C =100°C	Continuous Drain Current	71	A
I _{DM}	Pulsed Drain Current	440	A
EAS	Single Pulse Avalanche Energy (Note 1)	2531	mJ
P _D @T _C =25°C	Total Power Dissipation	330	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient (min. footprint)	---	45	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	0.38	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	200	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=50A$	---	8.2	10	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=200V$, $V_{GS}=0V$	---	---	1	uA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	46	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	3.2	---	Ω
Q_g	Total Gate Charge	$V_{DS}=100V$, $I_D=60A$ $V_{GS}=10V$	---	74	---	nC
Q_{gs}	Gate-Source Charge		---	30	---	
Q_{gd}	Gate-Drain Charge		---	16	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DS}=100V$, $V_{GS}=10V$, $I_D=50A$ $R_G=2.7\Omega$	---	35	---	ns
T_r	Rise Time		---	111	---	
$T_{d(off)}$	Turn-Off Delay Time		---	84	---	
T_f	Fall Time		---	112	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	5300	---	pF
C_{oss}	Output Capacitance		---	3100	---	
C_{rss}	Reverse Transfer Capacitance		---	140	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Diode continuous forward current	$V_G=V_D=0V$, Force Current	---	---	110	A
$I_{S,pulse}$	Diode pulse current		---	---	440	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_F=50A$, $T_J=25^{\circ}\text{C}$	---	0.82	1.4	V

Note :

1.The EAS data shows Max. rating .The test condition is $V_{DS}=80V$, $V_{GS}=10V$, $L=10\text{mH}$, $I_{AS}=22.5A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.

Typical Characteristics

