








NOTES:

备注


- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 60A
额定电流: 60A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

XD - * * * * - **** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	D=DIP	Product No.	Material
M=Full Teeth (插牙) R=NoFull Nut (无螺母) RG=Rivet Gasket (铆垫片)	3=M3 (螺牙) 4=M4 (螺牙) 5=M5 (螺牙) 6=M6 (螺牙) 8=M8 (螺牙)	2=2个 4=4个 6=6个 8=8个	0808=8x8mm (防止扭动)	1014=10x14mm	S=SMT FD=Flag DIP	产品序号	默认=Copper (黄铜) RC=Red Copper (紫铜)



GENERAL TOLERANCE		制图	02		XD 深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd		
DIM	TOL	审核			产品名称	版本	A
X.X	±0.30	CHECK			TITLE	REV.	
X.XX	±0.20	批准			PCB 焊接端子 (插板 铆垫片 M4 4焊脚 11.1x9.2x10.5mm)		
X.XXX	±0.10	APPROVAL			产品料号	单位	mm
Angle	±3.0°	比例			PART NO.	UNITS	
		SCALE			XD-RG44-1109-D061-02		
		投影			材料	页次	1/1
		Projection			MATERIAL	SHEET	