Surface-Mount Device

SL1210600

Version: 1.0
Document code: HB-WI7.3-268-2015
Effective date: 2015-12-27

Page: 1 of 3

ROHS 💝

# Feature

- Resettable over current and over temperature protection
- Small size of 1210
- Fast time-to-trip
- Small footprint
- ROHS complaint
- Low resistance

## **Application**


- Computer
- Battery
- Mobile phones

- Industrial controls
- AutomotivePortable electronics
- Multimedia
  - Game machines
  - Telephony and broadband

# **Part Numbering**



### **Product Dimensions in Millimeter**



Part Number	Α		В		С		D		E	
Part Number	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
SL1210600	3.00	3.50	2.35	2.85	0.6	1.5	0.25		0.10	

### **Electrical Characteristics**

I(A)		V <sub>max</sub>	I max	$Pd_{typ}$	T <sub>trip</sub>		R <sub>min</sub>	R <sub>1max</sub>	
Part Number	25	${}^{\circ}\mathbb{C}$				25	<b>25</b> ℃		${\mathbb C}$
	Hold	Trip	(V)	(A)	(W)	Current(A)	Time(S)	(Ω)	(Ω)
SL1210600	6.00	12.0	6.0	50	1.5	20.0	5.0	0.0008	0.009



Version: 1.0

Document code: HB-WI7.3-268-2015

Effective date : 2015-12-27

Page: 2 of 3

#### **Surface-Mount Device**

#### SL1210600

ROHS 🐃

I<sub>H</sub>=Hold current: maximum current at which the device will not trip at 25 °C still air reflow soldering of 260 °C for 20 sec.

I<sub>T</sub>=Trip current: minimum current at which the device will always trip at 25℃ still air reflow soldering of 260℃ for 20 sec.

V<sub>max</sub>=Maximum continuous voltage device can withstand without damage at rated current

I<sub>max</sub>=Maximum fault current device can withstand without damage at rated voltage.

 $T_{trip}$ =Maximum time to trip(s) at assigned current reflow soldering of 260  $^{\circ}$ C for 20 sec.

Pd<sub>typ</sub>=Typical power dissipation: typical amount of power dissipated by the device when in state air environment.

R<sub>min</sub>= Minimum resistance of device in initial (un-soldered) state.

 $R_{1max}$ =Maximum resistance of device at 25°C measured one hour after reflow soldering of 260°C for 20 sec.

Value specified is determined by using the PWB with 0.030 \*1.5oz copper traces.

Caution: Operation beyond the specified rating may result in damage and possible arcing and flame.


### **Environmental Specifications**

Test	Test Conditions	Accept /Reject Criteria	
Recommended storage conditions	40°C max, 70% R.H. max	No change	
Passive aging:	85°C, 1000 hours	≤ R <sub>1max</sub>	
Moisture Resistance	85% RH,85℃,1000hrs	≤ R <sub>1max</sub>	
Thermal Shock	MIL-STD-202 Method 107G +85°C /-40°C 20 times	≤ R <sub>1max</sub>	
Vibration	MIL-STD-883C, Method 2007.1, Condition A	No change	
Solvent Resistance	MIL-STD-202, Method 215	No change	
Moisture Level Sensitivity	Level 1, J-STD-020C	No change	

### Thermal Derating [ Hold Current (A) at Ambient Temperature (°C)]

Part Number	Maximum Ambient Operating Temperature (℃)								
Part Number	-40	-20	0	25	40	50	60	70	
SL1210600	9.0	8.0	7.0	6.0	5.2	4.6	4.2	3.7	

### **Solder Reflow Recommendation**





Version: 1.0

Document code: HB-WI7.3-268-2015

Effective date: 2015-12-27

Page: 3 of 3

#### **Surface Mount Device**

**SL1210600** 

ROHS 🐃

Recommended reflow methods:IR,hot air oven ,nitrogen oven

Devices can be cleaned using standard industry methods and solvents.

#### NOTE:

If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame

### **Packaging Quantity**

Device	Standard Quantity (pcs)
SL1210600	3000

# CAUTION:

Operation beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame. The devices are intended for protection against occasional over-current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated. Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.

### **Contact information**

SEA & LAND ELECTRONIC CORP.

13F., No.120-10, Sec. 3, Zhongshan Rd., Zhonghe Dist., New Taipei City 235, Taiwan

Tel:886-2-82212567 Fax:886-2-22257268

Rev. letter		Date	
Design	Check	Audit	Approve