

AlGaAs PIN MMIC Digital Attenuator Die, 3-Bit, Parallel Control, 1 dB LSB, 80 - 100 GHz, 7 dB Attenuation Range



MAAD-011038-DIE

Rev. V2

Features

- 3-Bit Digital Attenuator, 1 dB LSB
- 7 dB Attenuation Range
- Wide Frequency Range: 80 - 100 GHz
- Parallel Control:
 - Complementary Controls (per bit)
- Attenuation Accuracy:
 - $\pm(0.5 + 5\% \text{ of Attenuation Setting}) \text{ dB}$
- Die Size: 2.88 x 1.02 mm

Applications

- MMW Radios
- Automotive Radars
- Radiometry
- Passive Imaging
- SATCOM
- MMW Test Equipment
- General Purpose


Description

The MAAD-011038-DIE is a wide band 3-bit, 1 dB step AlGaAs PIN MMIC digital attenuator covering a large frequency range from 80 to 100 GHz with excellent insertion loss and attenuation accuracy.

Ordering Information

Part Number	Package
MAAD-011038-DIE	Die in Gel Pack

Functional Schematic



Pin Configuration

Pin #	Function	Description
1, 3, 4, 6	GND	Ground ¹
2	RF IN	Input RF
5	RF OUT	Output RF
7	V4A	4 dB Control A
8	V4B	4 dB Control B
9	V2A	2 dB Control A
10	V2B	2 dB Control B
11	V1A	1 dB Control A
12	V1B	1 dB Control B

1. All GND pins are connected to the chip's back side thru substrate vias.

¹ * Restrictions on Hazardous Substances, compliant to current RoHS EU directive.

AlGaAs PIN MMIC Digital Attenuator Die, 3-Bit, Parallel Control, 1 dB LSB, 80 - 100 GHz, 7 dB Attenuation Range



MAAD-011038-DIE

Rev. V2

Electrical Specifications: Freq. = 80 - 100 GHz, $T_A = 25^\circ\text{C}$, $Z_0 = 50\ \Omega$, $P_{IN} = 0\ \text{dBm}$

Parameter	Test Conditions	Units	Min.	Typ.	Max.
Reference Insertion Loss	—	dB	—	5	6
Attenuation Accuracy	Relative to Insertion Loss	$\pm (0.5 + 5\% \text{ of attenuation setting})\ \text{dB typ.}$			
Return Loss	All states (worst case)	dB	—	12	—
Input P0.1dB	Reference State	dBm	—	21	—
IIP ₃	2-Tone, +10 dBm/tone, 1 MHz Spacing (Reference State)	dBm	—	38	—
Control Voltage	HI @ 20 mA per BIT max. LOW @ 20 mA per BIT max.	V	— -5	1.3 —	1.7 0

Truth Table²

1 dB BIT		2 dB BIT		4 dB BIT		Attenuation (dB)
V1A	V1B	V2A	V2B	V4A	V4B	
0	1	0	1	0	1	Reference IL
1	0	0	1	0	1	1
0	1	1	0	0	1	2
0	1	0	1	1	0	4
1	0	1	0	1	0	7

2. "0" = 0 V, "1" = 1.3 V.

Absolute Maximum Ratings^{3,4}

Parameter	Absolute Maximum
Input Power 80 - 100 GHz	29 dBm
Control Voltage	$-5.5\ \text{V} \leq V_C \leq 1.7\ \text{V}$ @ 50 mA max.
Junction Temperature	+150°C
Operating Temperature	-55°C to +85°C
Storage Temperature	-65°C to +150°C

3. Exceeding any one or combination of these limits may cause permanent damage to this device.
4. MACOM does not recommend sustained operation near these survivability limits.

Handling Procedures

Please observe the following precautions to avoid damage:

Static Sensitivity

These electronic devices are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these HBM Class 1A devices.

AlGaAs PIN MMIC Digital Attenuator Die, 3-Bit, Parallel Control, 1 dB LSB, 80 - 100 GHz, 7 dB Attenuation Range




MAAD-011038-DIE


Rev. V2

Typical Performance Curves


Relative Attenuation




Thru S-Parameters



S11 (All States)



S22 (All States)




AlGaAs PIN MMIC Digital Attenuator Die, 3-Bit, Parallel Control, 1 dB LSB, 80 - 100 GHz, 7 dB Attenuation Range



MAAD-011038-DIE

Rev. V2

Outline Drawing



Bond Pad Dimensions (μm)

Pad	X	Y
1, 3, 4, 6	92	81
2, 5	79	50
7 - 12	58	58

Unless otherwise specified, all dimensions shown are μm with a tolerance of ±5 μm.

Die thickness is 100 μm ±10 μm.

Bond pad/backside metallization is gold.

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.