




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24





Technical Data

Material:
Contact Material:Copper Alloy
Contact Plating: Au or Sn Over Ni
Insulator Material:PPS UL94V-0

Electrical:
Rating current:3Amps/contact max
Rating voltage:60V AC/DC
Contact resistance:≤20MΩ/contact
Insulation resistance:≥1000MΩ
withstanding Voltage:500V AC/minute

Mechanical:
Operaing temperatures:Gold Plated:-55℃ to +105℃
Tin Plated:-40℃ to +105℃
Soldering temperature:+260℃ MAX(PPS)

Ordering Code:
MF254R-11-XX-1243-H70
1 2
1.序列号
2.Pin位数: 02x40P



P.C.B LAYOUT

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: MF254R-11-XX-1243-H70		XFCN 兴飞连接器		
TITLE: 2.54mm Machined Female Header		0769-82001899		
		www.xfconn.com		
		DWG NO: /		
APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.09.14	NONE	1/1	A1