

General Description

The 100N03B uses advanced trench technology to provide excellent $R_{DS(ON)}$ and low gate charge. This device is suitable for use as a wide variety of applications.

Features

- Simple Drive Requirement
- Fast Switching
- Low On-Resistance

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	30	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current	100	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current	70	A
I_{DM}	Pulsed Drain Current ¹	400	A
EAS	Single Pulse Avalanche Energy ²	400	mJ
P_D	Total Power Dissipation	120	W
T_{STG}	Storage Temperature Range	-55 to 175	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	175	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JC}$	Thermal Resistance Junction-case	---	1.04	$^\circ\text{C}/\text{W}$


Product Summary

BVDSS	$R_{DS(ON)}$	ID
30V	4m Ω	100A

Applications

- Uninterruptible Power Supply
- DC Motor Control
- Load Switch

TO-252/251 Pin Configuration



Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	30	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=20A$	---	---	4	$m\Omega$
		$V_{GS}=4.5V$, $I_D=20A$	---	---	6	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1	---	3	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=24V$, $V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=5V$, $I_D=15A$	---	32	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1MHz$	---	2	---	Ω
Q_g	Total Gate Charge	$I_D=30A$	---	67	---	nC
Q_{gs}	Gate-Source Charge	$V_{DD}=15V$	---	10	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	18	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=15V$	---	20	---	ns
T_r	Rise Time	$I_D=30A$	---	60	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=12\Omega$	---	110	---	
T_f	Fall Time	$V_{GS}=10V$	---	85	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1MHz$	---	3200	---	pF
C_{oss}	Output Capacitance		---	350	---	
C_{rss}	Reverse Transfer Capacitance		---	300	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	100	A
I_{SM}	Pulsed Source Current		---	---	400	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=20A$, $T_J=25^{\circ}\text{C}$	---	---	1.2	V

Note :

1.Repetitive rating; pulse width limited by maximum junction temperature

2.The test condition is $V_D=15V$, $L=0.5mH$, $I_D=40A$

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.

Typical Characteristics

