1W isolated DC/DC converter in SIP package Wide input and regulated dual/single output





EN62368-1 BS EN62368-

FEATURES

- Ultra compact SIP package
- Wide input voltage range (2:1)
- Operating temperature range: -40°C to +85°C
- I/O Isolation test voltage: 1.5k VDC
- Low ripple & noise
- Short-circuit protection (self-recovery)
- Remote On/Off

WRA_S-1WR2 & WRB_S-1WR2 series are isolated 1W DC-DC converter productions with a wide 2:1 input voltage range and input isolation is tested with 1500VDC. The product has a relatively compact SIP-8 plastic package, and features high efficiency, operating temperature of -40°C to +85°C, remote control, and continuous short-circuit protection. The smaller size and cost-effective design make the converter an ideal solution in communication, instruments, and industrial electronics applications.

RoHS

		Input Volta	ge (VDC)	Out	put	Ripple & Noise	Full Load	Capacitive
Certification	Part No.	Nominal (Range)	Max. ^①	Voltage(VDC)	Current(mA) Max./Min.	(mVp-p) Typ./Max.	Efficiency (%)Min./Typ.	Load [®] (µF)Max.
	WRA0505S-1WR2			±5	±100/±5		71/73	1000
	WRA0512S-1WR2			±12	±42/±2		74/76	470
	WRA0515S-1WR2			±15	±33/±2		73/75	330
	WRB0503S-1WR2	5 (4.5-9)	11	3.3	303/15	70/100	69/71	1800
	WRB0505S-1WR2		11	5	200/10	70/100	70/72	2200
	WRB0512S-1WR2			12	83/4		74/76	1000
	WRB0515S-1WR2			15	67/3		73/75	680
	WRB0524S-1WR2			24	42/2		71/73	470
	WRA1205S-1WR2	12 (9-18)	20	±5	±100/±5	100/150	75/77	1000
	WRA1212S-1WR2			±12	±42/±2		79/81	470
	WRA1215S-1WR2			±15	±33/±2		76/78	330
	WRB1203S-1WR2			3.3	303/15		73/75	2700
EN	WRB1205S-1WR2			5	200/10		75/77	2200
EIN	WRB1209S-1WR2			9	111/6		77/79	1800
	WRB1212S-1WR2			12	83/4		76/78	1000
	WRB1215S-1WR2			15	67/3		78/80	680
	WRB1224S-1WR2			24	42/2		74/76	470
	WRA2405S-1WR2			±5	±100/±5		77/79	1000
	WRA2409S-1WR2			±9	±56/±3		77/79	680
	WRA2412S-1WR2			±12	±42/±2		76/78	470
	WRA2415S-1WR2			±15	±33/±2		76/78	330
	WRB2403S-1WR2	24 (18-36)	40	3.3	303/15	70/100	73/75	2700
	WRB2405S-1WR2	(15 00)		5	200/10		75/77	2200
	WRB2412S-1WR2			12	83/4		76/78	1000
	WRB2415S-1WR2			15	67/3		76/78	680
	WRB2424S-1WR2			24	42/2		75/77	470

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

DC/DC Converter WRA_S-1WR2 & WRB_S-1WR2 Series

MORNSUN®

	WRA4805S-1WR2	48 (36-75)	i an	±5	±100/±5	100/150	74/76	1000
	WRA4812S-1WR2			±12	±42/±2		76/78	470
	WRA4815S-1WR2			±15	±33/±2		78/80	330
EN/BS EN	WRB4803S-1WR2			3.3	303/15		73/75	2700
	WRB4805S-1WR2			5	200/10		74/76	2200
	WRB4812S-1WR2			12	83/4		78/80	1000
	WRB4815S-1WR2			15	67/3		77/79	680

Notes: ①Exceeding the maximum input voltage may cause permanent damage;

②For the dual output modules, the capacitive loads of positive and negative outputs are the same.

Input Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
	5VDC Input	-	281/40	290/60		
land the Command (fill land (a.e. land)	12VDC Input	-	111/15	114/30		
Input Current (full load/no-load)	24VDC Input	-	55/6	57/10		
	48VDC Input		27/4	28/6	mA	
	5VDC Input		30		IIIA	
Deflected Dipple Current	12VDC Input		40			
Reflected Ripple Current	24VDC Input	-	55	-		
	48VDC Input	-	45	-		
	5VDC Input	-0.7		12	VDC	
Curao Voltago (logo may)	12VDC Input	-0.7		25		
Surge Voltage (1sec. max.)	24VDC Input	-0.7		50		
	48VDC Input	-0.7		100		
	5VDC Input	-		4.5		
Startin a Valtaga	12VDC Input	-		9		
Starting Voltage	24VDC Input	-		18		
	48VDC Input	-		36		
Input Filter			Filter capacitor			
Hot Plug			Unavailable			
Ctrl*	Module on		Ctrl pin open (high resistance	e)	
O.III	Module off	Ctrl pin pu	Ctrl pin pulled high (current 5-10mA typ. into Ctrl.)			

Item	Operating Condition	Operating Conditions		Тур.	Max.	Unit
Outrout Valtaria Annuara	5%-100% load, Input voltage range	3.3V/5V output		±2	±5	
Output Voltage Accuracy		others		±1	±3	
Linear Regulation	Input voltage variation from low to high at full load			±0.2	±0.5	%
Load Regulation	5%-100% load			±0.4	±0.75	
Transient Recovery Time	25% load step change			0.5	2	ms
Transient Response Deviation				±2.5	±5	%
Temperature Coefficient	Full load			±0.02	±0.03	%/℃
Short Circuit Protection			Continuous,	self-recovery		





General Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
Isolation	Input-output, with the test time of 1 minute and the leak current lower than 1mA	1500			VDC	
Insulation Resistance	Input-output, isolation voltage 500VDC	1000			ΜΩ	
Isolation Capacitance	Input-output, 100kHz/0.1V	-	120	-	pF	
Operating Temperature	see Fig. 1	-40		+85		
Storage Temperature		-55		+125	l °c	
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds			+300		
Storage Humidity	Non-condensing			95	%RH	
Switching Frequency (PFM Mode)	Full load, nominal input voltage		200		kHz	
MTBF	MIL-HDBK-217F@25℃	1000		-	k hours	


Mechanical Specifications				
Case Material	Black flame-retardant and heat-resistant plastic			
Dimension	22.00 x 9.50 x 12.00 mm			
Weight	4.5g(Typ.)			
Cooling Method	Free air convection			


Electro	magnetic Compo	atibility (EMC)		
Emissions	CE	CISPR32/EN55032	CLASS B (see Fig. 3-2) for recommended circuit)	
RE		CISPR32/EN55032	CLASS B (see Fig. 3-2) for recommended circuit)	
	ESD	IEC/EN61000-4-2	Contact ±4kV	perf. Criteria B
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN61000-4-4	±2kV (see Fig. 3-① for recommended circuit)	perf. Criteria B
Immunity	Surge	IEC/EN61000-4-5	line to line $\pm 2kV$ (see Fig. 3-1) for recommended circuit)	perf. Criteria B
IIIIIIIIIIIII	CS	IEC/EN61000-4-6	3 Vr.m.s	perf. Criteria A
	Voltage dips, short interruptions and voltage variations immunity	IEC/EN61000-4-29	0%, 70%	perf. Criteria B

Typical Characteristic Curves









Design Reference

21

24

27

Input Voltage (V)

33

36


60


55

50 18

1. Typical application

All DC-DC converters of this series are tested before delivery using the recommended circuit shown in Fig. 2. Input and/or output ripple can be further reduced by appropriately increasing the input & output capacitor values Cin and Cout and/or by selecting capacitors with a low ESR (equivalent series resistance). Also make sure that the capacitance is not exceeding the specified max. capacitive load value of the product.






Vin	5VDC&12VDC 24VDC&48VD			
Cin1	100µF/25V 10µF/100V			
Cin2	47μF/25V 1μF/100V			
Lin	4.7μH-12μH			
Cs	10μF-22μF/50V			
	Vo(3/±3/5/±5/9/±9V):100µF/16V			
Cout	Vo(12/±12/15/±15V):100µF/25V			
	Vo(24/±24V):100µF/50V			
Lout	2.2μH-10μH			
Cd	47nF/100V			

Fig. 2

2. EMC compliance circuit



Parameter description:

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

Model	Vin: 5VDC	Vin: 12VDC	Vin: 24VDC	Vin: 48VDC		
FUSE	Slow-blow, selecting based on needs					
MOV		\$14K25 \$14K35				
C0	1000µF/16V	1000μF/16V 1000μF/25V 330μF/50V				
C1	4.7μF/50V 4.7μF/100'					
LDM1	12µH					
C2	4.7μF/50V 4.7μF/100V					
C3	Refer to the Cout in Fig.2					
CY1	1nF/2kV					
D1	60V/1A					
	In accordance with the formula:					
R	$R = \frac{V_C - V_D - 1.0}{I_C} - 300$					
Cd	47nF/100V					

Notes:

3. Ctrl end

The modules are of normal output when the Ctrl end is suspended or of high resistance; the modules turn off when connecting with high level (relative to the input grounding); notice that the current flows into the pin shall be 5 - 10mA, the modules will be permanently damaged if the current exceeds its max. value (20mA in general).


The value of R can be derived as follows:

$$R = \frac{V_C - V_D - 1.0}{I_C} - 300$$

For Detailed parameter, please refer to EMC solution-recommended circuit in this manual.

4. Input current

When the electricity is provided by the unstable power supply, please make sure that the range of the output voltage fluctuation and the ripple voltage of the power supply do not exceed the indicators of the modules. Input current of power supply should afford the flash startup current of this kind of DC/DC module(see Fig. 5).



5. Output load requirements

When using, the minimum load of the module output should not be less than 5% of the nominal load. In order to meet the performance parameters of this datasheet, please connect a 5% dummy load in parallel at the output end, the dummy load is generally a resistor, please note that the resistor needs to be used in derating.

6. For additional information please refer to DC-DC converter application notes on www.mornsun-power.com


① For EMC tests we use Part ① in Fig. 3 for immunity and part ② for emissions test. Selecting based on needs.


 $[@]V_C$ is the voltage of the Ctrl end relative to the GND of the input grounding; V_D is the positive-going conduction pressure drop of D1; I_C is the current flows into the Ctrl end and its value is generally 5-10mA, see Fig. 3-@ for the peripheral circuit of Ctrl end;

③ If there is no recommended parameters, no external component is required.



Dimensions and Recommended Layout






Note:

Unit: mm[inch]

Pin section tolerances: $\pm 0.10[\pm 0.004]$ General tolerances: $\pm 0.25[\pm 0.010]$





Note: Grid 2.54*2.54mm

Pin-Out				
Pin	Single	Dual		
1	GND	GND		
2	Vin	Vin		
3	Ctrl	Ctrl		
5	NC	NC		
6	+Vo	+Vo		
7	OV	OV		
8	CS	-Vo		

WR_XS-1WR2 Series without Pin 3 and Pin 5 NC: Not available for electrical connection

Notes:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging number: 58210004;
- 2. Recommend to use module with more than 5% load, if not, the ripple of the product may exceeds the specification, but does not affect the reliability of the product;
- The recommended unbalance degree of the dual output module load is ≤±5%; if the degree exceeds ±5%, then the product
 performance cannot be guaranteed to comply with all parameters in the datasheet. Please contact our technicians directly for
 specific information;
- 4. The maximum capacitive load offered were tested at input voltage range and full load;
- 5. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 6. All index testing methods in this datasheet are based on company corporate standards;
- 7. We can provide product customization service, please contact our technicians directly for specific information;
- 8. Specifications are subject to change without prior notice.

Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail: info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.