

SILICON BRIDGE RECTIFIERS

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Ideal for printed circuit boards
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 260°C/10 seconds, 5 lbs. (2.3kg) tension

Mechanical Data


Case : JEDEC KBPC-8/BR-8 Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 1.02 ounce, 29 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD KBPC15005	MDD KBPC1501	MDD KBPC1502	MDD KBPC1504	MDD KBPC1506	MDD KBPC1508	MDD KBPC1510	UNITS
Marking Code									
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	30	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward output rectified current at $T_c=55^\circ\text{C}$ (Note 1)	$I_{(AV)}$	15.0							A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	300							A
Rating for Fusing ($t < 8.3\text{ms}$)	I^2t	373							A ² s
Maximum instantaneous forward voltage drop per bridge element at 7.5A	V_F	1.1							V
Maximum DC reverse current $T_A=25^\circ\text{C}$ at rated DC blocking voltage $T_A=100^\circ\text{C}$	I_R	10							μA
		1.0							mA
Isolation voltage from case to leads	V_{IOS}	2500							V _{AC}
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	2.0							°C/W
Operating junction temperature range	T_J	-65 to +150							°C
storage temperature range	T_{STG}	-65 to +150							°C

NOTES:

1. Unit mounted on 5" x 4" x 3" thick (12.8cm x 10.2cm x 7.3cm) Al. plate.

2. Bolt down on heat-sink with silicone thermal compound between bridge and mounting surface for maximum heat transfer efficiency with #8 screw.

Ratings And Characteristic Curves

FIG.1-DERATING CURVE FOR
OUTPUT RECTIFIED CURRENT




FIG.2-MAXIMUM FORWARD SURGE CURRENT




FIG.3-TYPICAL FORWARD
CHARACTERISTICS





FIG.4-TYPICAL REVERSE
CHARACTERISTICS



The curve above is for reference only.