





RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



CIRCUIT DIAGRAM

E	按钮	PPA	1	白/黑色
D	盖板	铜盖板	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	白/黑色
A	卡件	黄铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR



PCB.WELDING DRAWING

The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	$\leq 100\text{m}\Omega$
Operating force	$\pm 50\text{gf}$
Travel	$0.20 \pm 0.10\text{mm}$
Insulated resistance	$\geq 100\text{M}\Omega$
Dielectric strength	$\geq 250\text{VAC}/1\text{min}$

TS50120-413-AA

按力码
100=10
150=15
280=28

高度码
H4. 3=043
H4. 5=045
H5. 0=050

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X.X ± 0.35	X. $^{\circ}$ $\pm 5^{\circ}$	PART NO.	TITLE:	
.XX ± 0.25	X.X $^{\circ}$ $\pm 3^{\circ}$	TS50120-413-AA	3x6 DIP TACT SWITCH	
.XXX ± 0.15	X.XX $^{\circ}$ $\pm 1^{\circ}$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		A4
		APPD: Sophia	SCALE	UNITS
				MM
			SHEET	1/1