

MBR10100xx

Schottky Barrier Rectifiers


Features

- Low forward voltage
- High current capability
- High forward surge capability
- Low power losses, High efficiency
- Guarding for over voltage protection

Applications

Low VF Schottky barrier rectifier are designed for high frequency, miniature switched mode power supplies such as adapters, lighting and on-board DC/DC converters.

Package



Mechanical Data

- Molded Plastic: UL Flammability Classification Rating 94V-0
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Solder bath temperature 265°C maximum, 10s per JESD 22-B106
- Case: Molded plastic
- Polarity: As marked
- Mounting Position: Any

Ordering information

Order code	Package	Base qty	Delivery mode
MBR10100CT	TO-220AB	50 pcs/tube	1000pcs/box 5000pcs/carton
MBR10100FCT	TO-220F	50 pcs/tube	1000pcs/box 5000pcs/carton
MBR10100BCT	TO-263	50 pcs/tube	1000pcs/box 5000pcs/carton
MBR10100BCT-R	TO-263	800 pcs/reel	800pcs/box 4000pcs/carton
MBR10100DCT	TO-252	2500 pcs/reel	2500pcs/box 12500pcs/carton



MBR10100xx

Schottky Barrier Rectifiers

Maximum Ratings (@ $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameters	Value	Unit
V_{RRM}	Rcurrent Peak Reverse Voltage	100	V
V_{RWM}	Working Peak Reverse Voltage	100	V
V_{DC}	DC Blocking Voltage	100	V
I_O	Average Forward Rectified Current(Per Leg)	5	A
	Average Forward Rectified Current(Total)	10	
I_{FSM}	Peak forward surge current 8.3 ms single half sine-wave	200	A
T_j	Operating junction temperature	150	$^{\circ}\text{C}$
T_{STG}	Storage temperature range	-55 to +150	$^{\circ}\text{C}$
$R_{\theta JC}$	Typical Thermal Resistance ⁽¹⁾ (TO-220AB,TO-263,TO-252)	2	$^{\circ}\text{C/W}$
	Typical Thermal Resistance ⁽¹⁾ (TO-220F)	4	

Note:(1)Thermal resistance from Junction to case per leg mounted on heatsink.

Electrical Characteristics (@ $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameters	Test conditions	Typ	Max	Unit
V_F	Forward Voltage ⁽²⁾	$I_F=2A, T_A=25^{\circ}\text{C}$	0.68	—	V
		$I_F=2A, T_A=125^{\circ}\text{C}$	0.56	—	
		$I_F=3A, T_A=25^{\circ}\text{C}$	0.72	—	
		$I_F=3A, T_A=125^{\circ}\text{C}$	0.60	—	
		$I_F=5A, T_A=25^{\circ}\text{C}$	0.76	0.85	
		$I_F=5A, T_A=125^{\circ}\text{C}$	0.65	—	
I_R	Reverse Current	$V_R=100V, T_A=25^{\circ}\text{C}$	1	5	μA
		$V_R=100V, T_A=125^{\circ}\text{C}$	0.6	—	mA

Note:(2)Pulse test: 300 μs pulse width, 1% duty cycle.



MBR10100xx

Schottky Barrier Rectifiers

Typical Performance Characteristics($T_A = 25^\circ\text{C}$, unless otherwise noted)

Figure 1:MAX. Forward Current Derating Curve




Figure 2:MAX. Non-Repetitive Forward Surge Current




Figure 3:Typical Forward Characteristics






Figure 4:Typical Reverse Characteristics



MBR10100xx


Schottky Barrier Rectifiers

Packaging Tape - TO-220AB



Symbol	Millimeters		
	MIN.	TYP.	MAX.
A	4.30	4.50	4.70
A1	2.52	2.67	2.82
b	0.71	0.81	0.91
b1	1.17	1.27	1.37
C	0.30	0.40	0.50
C1	1.17	1.27	1.37
D	9.90	10.00	10.20
E	8.50	8.70	8.90
E1	12.00	12.25	12.50
e	2.44	2.54	2.64
e1	4.88	5.08	5.26
F	2.60	2.75	2.80
L	13.00	13.50	14.00
L1	3.80	4.00	4.20

Packaging Tape - TO-220F




Symbol	Millimeters		
	MIN.	TYP.	MAX.
A	4.30	4.60	4.80
A1	2.70	2.80	2.90
b	0.70	0.80	0.90
b1	1.20	1.30	1.40
C	0.40	0.50	0.60
C1	2.40	2.60	2.80
D	9.90	10.00	10.20
E	15.20	15.60	16.00
e	2.44	2.54	2.64
e1	4.88	5.08	5.26
F	3.00	3.30	3.60
L	12.70	13.20	13.70
L1	2.70	2.90	3.10
d	3.10	3.20	3.30



MBR10100xx

Schottky Barrier Rectifiers

Packaging Tape - TO-263




Symbol	Millimeters		
	MIN.	TYP.	MAX.
A1	0	—	0.25
B	1.32	1.37	1.42
b	—	1.27	—
b1	1.30	1.40	1.45
b2	—	0.81	—
C	4.52	4.57	4.62
C1	—	1.27	—
C2	2.64	2.69	2.74
C3	—	0.38	—
D	10.11	10.16	10.21
E	10.02	10.07	10.12
e	—	2.54	—0
L	14.65	14.95	15.25
L1	4.60	4.90	5.20
L2	2.25	2.45	2.65
L3	1.10	1.30	1.50
Θ	6°	7°	8°
Θ1	6°	7°	8°
Θ2	0°	—	8°
Θ3	2°	3°	4°
Θ4	2°	3°	4°
Θ5	—	—	20°



MBR10100xx

Schottky Barrier Rectifiers

Packaging Tape - TO-252



Symbol	Millimeters		Inches	
	MIN.	MAX.	MIN.	MAX.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
ϕ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	

