


# PIN RECEPTACLES

FOR 0,38 - 0,56 DIAMETER PINS

## 0512

0512-0-15-XX-12-XX-04-0


Press-fit in 1,45 mounting hole



## 0703

0703-0-15-XX-12-XX-04-0


Press-fit in 1,45 mounting hole



## 0574

0574-0-15-XX-12-XX-04-0


Press-fit in 1,45 mounting hole



## 0468 \*

0468-0-15-XX-12-XX-04-0


Press-fit in 1,45 mounting hole



## 8894 \*

8894-0-15-XX-12-XX-10-0


Hex press-fit in 1,5 plated through-hole



## 0550 \*

0550-0-15-XX-22-XX-10-0


Solder mount in 1,32 min. mounting hole  
Also available on 16mm wide carrier tape:  
1,700 parts per 330mm reel  
Order as: 0550-0-57-XX-22-XX-10-0



## 0671 \*

0671-0-15-XX-12-XX-10-0


Solder mount in 1,6 min. mounting hole



## 0707 \*

0707-0-15-XX-12-XX-10-0


Solder mount in 1,3 min. mounting hole




## 5739 \*

5739-0-18-XX-12-XX-10-0

Surface mount  
Also available on 16mm wide carrier tape:  
3,000 parts per 330mm reel  
Order as: 5739-0-58-XX-12-XX-10-0




P.C.B. Layout



## 1534

1534-X-15-XX-12-XX-04-0

Press-fit in 1,42 mounting hole



| Basic Part Number | Length A |
|-------------------|----------|
| 1534-0            | 2,41     |
| 1534-1            | 3,18     |

### SPECIFICATIONS:

**Shell Material:** Brass Alloy 360, 1/2 Hard

**Contact Material:** Beryllium Copper Alloy 172, HT

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$

Diameters:  $\pm 0,051$

Angles:  $\pm 2^\circ$



**ORDER CODE:** XXXX - X - 1X - XX - XX - XX - 0

**BASIC PART #**

**SPECIFY SHELL FINISH:**

01 5,08 $\mu$ m TIN/LEAD OVER NICKEL

◆ 80 5,08 $\mu$ m TIN OVER NICKEL (RoHS)

◆ 15 0,25 $\mu$ m GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**

02 2,54 $\mu$ m TIN/LEAD OVER NICKEL

◆ 84 2,54 $\mu$ m TIN OVER NICKEL (RoHS)

◆ 27 0,76 $\mu$ m GOLD OVER NICKEL (RoHS)

**SELECT CONTACT:**

#12 or #22 CONTACT (DATA ON PAGE 252)

\* (Contact may be interchanged with group B or C contact on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com