



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:ABS BLACK

b.SPRING: STEEL





(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C



MOUNTING DETAIL

ORDERING INFORMATION

BH-AA-A5BJ012

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING

MATERIAL:

1A-PP BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK

5B-ABS BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND WangHeng	DATE 2024-11-30
WEIGHT:		CHKD ZhouRuicai	DATE 2024-11-30
SHEET 1 OF 1		APVD XueShunyong	DATE 2024-11-30
SCALE:		SIZE: A4	VIEW:
UNIT: mm		REV.: A/1	OBJECT: MY
TITLE:		电池盒BH-AA-1J Ni DIP	
PART NO.:		BH-AA-A5BJ012	
DRAW NO.:WD-CP-0116			

②	CONTACT	2	STEEL, 0.55MM	Ni-Plating
①	HOUSING	1	ABS Resin	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR