




ROHS



1. Electrical Characteristics

- 1.1 Impedance: 50 Ohm
- 1.2 Working Frequency: 0-6GHz
- 1.3 S.W.R.: ≤ 1.5
- 1.4 Working Voltage: 335V / max
- 1.5 Insulation Resistance: 1000 Mohm
- 1.6 Contact Resistance: Center Contact: 5 mohm
- 1.7 Outer Contact: ≤ 2.5 mohm


2. Environmental

- 2.1 Working Temperature Range: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$
- 2.2 Salt spray test: 48H

产品型号: DL-Q5-SMA-KE
产品材质: 黄铜 表面镀金

P. C. B LAYOUT

5	绝缘体	PTFE 白色
4	四角本體	黄铜 镀金
3	绝缘体	PTFE 白色
2	中心PIN	黄铜 镀金
1	螺牙本體	黄铜 镀金
部件序号	部件品名	材料

	 深圳市骏晔科技有限公司 SHENZHEN DREAMLNK TECHNOLOGY CO., LTD				
Tolerance 未注公差 .X ±0.30 .XX ±0.20 .XXX ±0.10 未注角度公差: ±1°			Part Name. 品名	DL-Q5-SMA-KE	
	Material. 材				
	Finish. 理				
	Scale. 比例	1:1	Draw .	Check. 校	App. 核准
	REV. 版本/次	A/0	20.03.15	20.03.15	20.03.15
	Unite. 位	mm			