

NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM PUSHOUT FORCE: 16 OZ FOR TERMINALS, 12 OZ FOR WELD TABS, AND 8 OZ FOR LOCKING CLIPS.
3. MEASURED FROM BEND.
4. MAXIMUM TERMINAL BURR: .003 [.08].
5. MAXIMUM HEIGHT VARIATION BETWEEN ANY TWO PINS: .005 [.13].
6. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.




TABLE 1

POSITION	COPLANARITY
-02 THRU -29	.004 [.10]
-030 THRU -39	.006 [.15]
-40 THRU -50	.008 [.20]

FIG 1
(TFM-115-01-X-S-XX SHOWN)

TABLE 2

LEAD STYLE	BODY	"A"	"B"	"C"	"E"
-01	TFM-XX-S-01-XX	.078 [1.98]	.131 [3.33]	.428 [10.87]	.303 [7.70]
-02	TFM-XX-S-01-XX	N/A	.131 [3.33]	.428 [10.87]	.231 [5.87]
-03	TFM-XX-S-01-XX	.111 [3.33]	.139 [3.53]	.645 [16.38]	.356 [9.04]

TFM-1XX-XX-X-S-XX

No OF POSITIONS
ALL POSITIONS AVAILABLE
-02 THRU -50

LEAD STYLE

- 01: T-1R16-01-X-2
THROUGH HOLE
- 02: T-1R16-01-X-2
SURFACE MOUNT
- 03: T-1R16-10-X
THROUGH HOLE



PLATING SPECIFICATIONS

- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3μ" FLASH GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- L: 15μ" LIGHT GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30μ" HEAVY GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL
- T: MATTE TIN CONTACT AND TAIL


- OPTION
 - A: ALIGNMENT PIN (USE TFM-XX-S-01-A) (NOT AVAILABLE WITH -WT OPTION) (SEE FIG 5, SHEET 2)
 - LC: LOCKING CLIP (USE LC-05-TM) (NOT AVAILABLE WITH -WT OPTION) (SEE FIG 7, SHEET 3) (SEE NOTE 6)
 - P: PICK AND PLACE PAD (USE PPP-15) (SEE FIG 6, SHEET 2) (ONLY AVAILABLE ON -08 THRU -50 POSITIONS)
 - K: POLYIMIDE FILM (SEE FIG 3, SHEET 2) (USE K-DOT-217-313-.005)
 - WT: WELD TABS (USE WT-25-07-T) (SEE FIG 4, SHEET 2) (AVAILABLE ON -02 THRU -30 POS ONLY) (NOT AVAILABLE WITH -A OR -LC OPTIONS)
 - TR: TAPE & REEL (SEE SHEET 3, TAPE AND REEL VIEW)
 - **SN: SOLDER NAIL (USE WT-27-03) (NOT AVAILABLE WITH -A, -LC, OR -WT OPTIONS) (SEE FIG 8, SHEET 3)

- BODY SPECIFICATION
 - S: SINGLE ROW (USE TFM-XX-S-XX-XX)

** NOT TOOLED



SECTION "A"- "A"



IN-PROCESS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1:0.4
INSULATOR: LCP, UL 94 V0, COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE

DESCRIPTION:
.050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP
DWG. NO.

TFM-1XX-XX-X-S-XX

BY: D. SCHMELZ 8/21/2008 SHEET 1 OF 3

Samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

REVISION AH





FIG 2
SURFACE MOUNT
(TFM-115-02-X-S-XX SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 4
-WT OPTION
(TFM-114-01-X-S-WT SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 5
-A OPTION
(TFM-115-02-X-S-A SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

NOTE: "R" = OVERALL LENGTH REF
"S" = (("R" - .216[5.49]) /2) ±.020[.51]




FIG 3
-K: POLYIMIDE FILM PAD
(TFM-115-02-X-S-K SHOWN)




FIG 6
-P OPTION
(TFM-115-02-X-S-P SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(PAD TO BE POSITIONED ON CL AS SHOWN)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 2:1

samtec



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION: .050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP


DWG. NO. TFM-1XX-XX-X-S-XX

BY: D. SCHMELZ 8/21/2008 SHEET 2 OF 3

REVISION AH




TAPE AND REEL VIEW



PACKAGING TUBE VIEW

NOTES:

1. USE PT-1-24-11-09 TUBE AND (2) TP-24.
2. USE PT-1-24-03-09 TUBE AND (2) TP-09 FOR -P AND -K OPTIONS.
3. LOAD TUBE WITH 1ST POSITION IN SAME DIRECTION AS ARROW



SECTION "G"- "G"
SCALE 3 : 1

FIG 8
** -SN OPTION
(TFM-110-02-X-S-SN SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

** NOT TOOLED





FIG 7
-LC OPTION
(TFM-115-01-X-S-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 2)



* INSPECT ONLY WHEN APPLICABLE WITH RESPECT TO ASSEMBLY OPTION

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.	
DO NOT SCALE DRAWING	
SHEET SCALE: 2:1	

DESCRIPTION: .050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP	
DWG. NO. TFM-1XX-XX-X-S-XX	
BY: D. SCHMELZ 8/21/2008 SHEET 3 OF 3	