

INTERCONNECTS

SERIES 351 • 2,54 GRID INTERCONNECT HEADERS • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3

- Series 351 interconnect header strips come in three lengths with 0,46 dia. pluggable solder tails at one end and 0,64 dia. pins at the other. Please see series:

351...003 uses pin #5503
351...004 uses pin #5504
351...005 uses pin #5505

- 0,46 pluggable solder tails are available at both ends. Please see series:

351...009 uses pin #5509
351...010 uses pin #5510
351...011 uses pin #5511

See pages 212 and 214 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 351...003	0,46 / 0,64 Dia. Solder Tails
	351-10-1	-00-003000
	Specify number of pins	01-64
FIG. 2	Series 351...009	0,46 / 0,46 Dia. Solder Tails
	351-10-1	-00-009000
	Specify number of pins	01-64
FIG. 3	Series 351...004	0,46 / 0,64 Dia. Solder Tails
	351-10-1	-00-004000
	Specify number of pins	01-64
FIG. 3	Series 351...010	0,46 / 0,46 Dia. Solder Tails
	351-10-1	-00-010000
	Specify number of pins	01-64
FIG. 3	Series 351...005	0,46 / 0,64 Dia. Solder Tails
	351-10-1	-00-005000
	Specify number of pins	01-64
FIG. 3	Series 351...011	0,46 / 0,46 Dia. Solder Tails
	351-10-1	-00-011000
	Specify number of pins	01-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating		
10 ◆		
0,25µm Au		