

D-USB Connectors

1

2

3

4

5

6

7

8

9

10

Specification

> Standard

(SDB) D-SUB

> High Density

(HDB) High Density D-SUB

Number of Contacts

09,15,,25,26...78 Contacts

Ex. 09 Pin = (09)

Connector Body (Style)

> For Receptacle

(P) Front Fastened

> For Overmolded with Cable

(A) With Strain Relief

> For Field installable

(B) Without Strain Relief

Connector (Housing) Gender

(M) Male Connector

(F) Female Connector

Contact Gender

(M) Male (Plug)

(F) Female (Jack)

Assemble Style

> For Receptacle

(S) Solder Type

(P) PCB Type (90° / 180°)

> For Overmolded with Cable

(M) Overmolded with Cable

> For Field Installable

(A) Field Installable (Solder)

(C) Field Installable (Crimped)

Mating Style

(S) Screw Thread

(Q) Automated Latch

Backshell

> For Receptacle

(With Board Lock)

(A) Straight

(B) Right Angle

(Without Board Lock)

(L) Straight

(R) Right Angle

> For Overmolded with Cable

(Without Board Lock)

(L) Straight

> For Field Installable

(Without Board Lock)

(L) Straight

Waterproof Rating

(7) IP 67

(8) IP 68

More Information

> For Receptacle

(001), (002).....

Without Cable : Different

Versions

> For Overmolded with Cable

(□)+(■) : Cable Type + Cable Length

EX. (A01) = UL2464 Cable + 1M

(□) : Cable Type

(A) UL2464 Cable

(■) : Cable Length

From 1M to 99M

EX. (01) = 1M