


PIN RECEPTACLES

FOR 1,22 - 1,63 DIAMETER PINS (#13 CONTACT)
FOR 1,14 - 1,65 DIAMETER PINS (#23 CONTACT)

0496

0496-0-15-XX-23-XX-10-0


Press-fit in 2,69 mounting hole



0368

0368-0-33-XX-13-XX-10-0


Wire crimp termination. Accepts wire sizes 16 AWG Max. / 20 AWG Min.



8067

8067-0-19-XX-13-XX-10-0


Wire Termination. Accepts wire sizes 24 AWG Max. / 28 AWG Min.



1105

1105-0-15-XX-13-XX-04-0


Press-fit in 2,03 mounting hole



8730

8730-0-19-XX-23-XX-10-0


Wire crimp termination. Accepts wire sizes 22 AWG Max. / 26 AWG Min.



3667

3667-0-19-XX-23-XX-10-0


Wire crimp termination. Accepts wire sizes 18 AWG Max. / 22 AWG Min.



9372

9372-0-15-XX-23-XX-10-0


Solder mount in 2,59 min. mounting hole



4582

4582-0-15-XX-23-XX-10-0


Square press-fit in 1,02 plated through-hole



5834

5834-0-15-XX-23-XX-10-0


Press-fit in 2,72 mounting hole



9401

9401-0-15-XX-23-XX-10-0


Solder mount in 2,59 min. mounting hole
 Also available on 24mm wide carrier tape:
 1,100 parts per 330mm reel
 Order as: 9401-0-57-XX-23-XX-10-0



9801

9801-0-15-XX-23-XX-10-0


Solder mount in 2,59 min. mounting hole
 Also available on 16mm wide carrier tape:
 1,200 parts per 330mm reel
 Order as: 9801-0-57-XX-23-XX-10-0



8829

8829-0-15-XX-23-XX-10-0

Solder mount in 2,59 min. mounting hole
 Also available on 24mm wide carrier tape:
 1,000 parts per 330mm reel
 Order as: 8829-0-57-XX-23-XX-10-0



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$

Diameters: $\pm 0,051$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25μm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76μm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#13 or #23 CONTACT (DATA ON PAGE 260)

(For alternate contact choices, see group G on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com